






LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	DWN
			P6	REVISED PER ECR-07-028917	04DEC07	GP



SECTION A-A

- 1
- PRODUCT PROVIDED IN STRIP FORM ON REELS;
BREAKS MAY BE PRESENT.
- 2
- WIRE RANGE: 3300 TO 9000 CMA
- 3
- CRIMP WIDTH: .140 F TYPE
CRIMP HEIGHT (±.002)=(TOTAL CMA+14,600)/223,200
FOR APPLICATOR INFORMATION CALL:1-800-722-1111
FOR PRODUCT INFORMATION CALL:1-800-522-6752

CU-NI-SI C70260	40509-1
BRASS C26000	40509
MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 21DEC06		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK G.D.PORTA 04JAN07			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G.D.PORTA 04JAN07		NAME SPLICE
	0 PLC ± -		PRODUCT SPEC		
	1 PLC ± -		—		
	2 PLC ± -		APPLICATION SPEC		
3 PLC ± 0.25 [.010]		—		SIZE	
4 PLC ± -		—		CAGE CODE	
ANGLES ± -		—		DRAWING NO	
MATERIAL		FINISH		RESTRICTED TO	
SEE TABLE		NONE		—	
CUSTOMER DRAWING				SCALE 10:1	
				SHEET 1 OF 1	
				REV P6	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[40509 \(Mouser Reel\)](#) [40509 \(Cut Strip\)](#)