



1. MAX. WIRE INSULATION USED IN THIS RECEPTACLE IS .068 DIA. FOR SIZE 20 SIGNAL CONTACTS.
  2. STAINLESS STEEL RETENTION CLIPS FOR SIGNAL CONTACTS ARE INCLUDED IN INSERT ASSY.
  3. USE 17 SIZE 20 SOCKET SIGNAL CONTACTS, AMP PART NO. 205090-1 OR ANY OF THE AMP PRECISION FORMED SIZE 20 SOCKET CONTACTS FOR AMPLIMITE CONNECTORS.
  4. USE 7 SIZE 8 POWER OR COAX SOCKET CONTACTS. CONSULT PRODUCT ENGINEERING FOR MORE DETAILS.
  5. CONNECTOR SUPPLIED WITHOUT CONTACTS; SHOWN FOR ILLUSTRATION ONLY.
  6. THIS RECEPTACLE WILL MATE WITH ANY 24C7, SIZE 5 PLUG IN AMPLIMITE SERIES.
- △ MATING FACE SIZE 8 PORTS CHAMFERED TO ACCOMODATE BLINDMATE APPLICATION. BLINDMATE PLUG P446631-1 WILL MATE WITH THIS CONNECTOR.

OBSOLETE	△	445000-2
	-	445000-1
	REMARKS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. YOHN 7-14-87	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
		CHK B. YOHN 7-15-87		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD A. EMADI 7-15-87	NAME	
	0. PLC ± -	PRODUCT SPEC	RECEPTACLE ASSEMBLY, AMPLIMITE, 24C7, SIZE 5, SERIES 109, COAX MIX,	
	1. PLC ± -	APPLICATION SPEC		
	2. PLC ± -			
MATERIAL SEE CALLOUTS	FINISH SEE CALLOUTS	WEIGHT -	SIZE A1	CAGE CODE 00779
CUSTOMER DRAWING		SCALE 4:1	SHEET 1	OF 1
		REV F		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[445000-1](#)