





LOC		DIST		REVISIONS					
—		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
					D	REV PER ECO-06-013796	26JUN06	PY	DM



1. THIS RECEPTACLE WILL MATE WITH ANY SIZE 3, 44 POSITION PLUG IN THE AMPLIMITE SERIES.
2. MAXIMUM WIRE INSULATION USED WITH THIS RECEPTACLE IS .054 DIA.
3. BE. CU. RETENTION CLIPS ARE INCLUDED IN INSERTS.
4. CONNECTOR SUPPLIED WITHOUT CONTACTS
5. TESTED PER 010648 TABLE II, 100% VISUAL & MECHANICAL INSPECTION, IR & DWV.
6. UL/CSA DESIGNATION STAMPED IN THIS AREA,OPTIONAL
7. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS. METRIC EQUIVAVANTS ARE BASED ON 1.00 INCH = 25.4 mm.



SOCKET CONTACT
MATERIAL: BERYLLIUM COPPER
PLATING: GOLD PER MIL-C-45204
OVER COPPER PER MIL-C-14550.



SOCKET CONTACTS INCLUDED		B010648-0006	446825-1
INK STAMP		CUSTOMER PART NO	PART NO
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SHUEY 9-20-89	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608
DIMENSIONS: INCHES		CHK A. EMADI 9-26-89	NAME RECEPTACLE ASSEMBLY, AMPLIMITE 44 POSITION, SERIES 90, NON-MAGNETIC WITH GROMMET AND SPECIAL TESTING
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH SEE CALLOUTS		APVD A. EMADI 9-26-89	SIZE A1
MATERIAL SEE CALLOUTS		WEIGHT -	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1 REV D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[446825-1](#)