




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		W	REV PER ECO 13-009837	6-13-13	CT	DM



--	.0445-.0485	.048-.052	.776	4-448139-3
	.044-.048	.059 MAX	.701	4-448139-0
	.044-.048	.059 MAX	.701	3-448139-9
--	.044-.048	.048-.052	.701±.005	3-448139-8
	.044-.048	.059 MAX	.617±.005	3-448139-5
	.044-.048	.059 MAX	.617±.005	3-448139-4
	.0445-.0485	.048-.052	.606	3-448139-3
--	.0445-.0485	.059 MAX	.826±.005	3-448139-0
	.0445-.0485	.048-.052	.826±.005	2-448139-9
--	.0445-.0485	.048-.052	.576	2-448139-5
	.0445-.0485	.059 MAX	.651	2-448139-2
--	.044-.048	.048-.052	.468±.005	2-448139-1
	.044-.048	.048-.052	.617±.005	1-448139-8
	.0445-.0485	.059 MAX	.536±.005	1-448139-5
--	.044-.048	.048-.052	.505±.005	1-448139-4
--	.0445-.0485	.048-.052	.536	1-448139-1
--	.0445-.0485	.0615-.0630	.415	448139-8
--	.0445-.0485	.048-.052	.651	448139-6
--	.0445-.0485	.048-.052	.536	448139-3
REMARKS	DIM C	DIM B	DIM A	PART NO.

- 1 ELECTRICAL ENGAGEMENT POINT.
- 2 THIS AREA SOLDER DIPPED.
- 3 MANUFACTURERS LOGO; LACATION & ORIENTATION OPTIONAL.
- 4 SOLDER IS RoHS-COMPLIANT Sn.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 270CT2009 C.C. THOMAS CHK 270CT2009 K. THACKSTON APVD 270CT2009 K. THACKSTON		 TE Connectivity			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME POSTED PIN CONTACT, SIZE 16, ARINC 6			
		0 PLC ±. 1 PLC ±. 2 PLC ±. 3 PLC ±.010 4 PLC ±. ANGLES ±. FINISH					
MATERIAL		WEIGHT -					
SEE TABLE		SEE CALLOUTS		SIZE A2 CAGE CODE 00779 DRAWING NO. C-448139		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 10:1		SHEET 1 OF 1 REV W	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-448139-6](#)