




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
DY	-		A	PER ECO-13-001490	03JUN13	BL AC



- 1 HOUSING: LCP, UL 94V-0 RATED, BLACK
CONTACTS: PHOSPHOR BRONZE
RETENTION LEGS: BRASS
- 2 0.76um MIN GOLD FOR A LENGTH 2.00 STARTING 1.00 MAX FROM MATING END, 3.81um MIN TIN FOR A LENGTH OF 3.43 MIN FROM OPPOSITE END, BOTH OVER 1.27um MIN NICKEL
- 3 3.81 um MIN TIN OVER 1.27um MIN NICKEL
- 4. RECOMMENDED PCB THICKNESS: 1.14±0.13mm
- 5 K, L AND M INDICATES NUMBER OF TERMINAL POSITIONS.
- 6 TOLERANCE APPLIES AT CONTACT MATING SURFACE.

OBSOLETE

OBSOLETE																		
TRAY	24.765	41	80	40	61.67	39	58.17	32.680	65.36	57.87	28.30	62.15	66.50	80	5084487-3			
TUBE	12.065	21	40	20	36.27	19	32.77	19.975	39.95	32.47	15.60	36.75	41.10	40	5084487-2			
TUBE	24.765	41	80	40	61.67	39	58.17	32.680	65.36	57.87	28.30	62.15	66.50	80	5084487-1			
PACKAGING	P	M	L	K	J	H	G	F	E	D	C	B	A	POS.	PART NO.			
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.			DWN WYLEE			19JAN05			tyco Electronics			Tyco Electronics Singapore Pte. Ltd.						
DIMENSIONS: mm			TOLERANCES UNLESS OTHERWISE SPECIFIED:			CHK VINCENT TAN			NAME									
			APVD SE L FONG			PRODUCT SPEC			PLUG ASSY, STRADDLE MOUNT, CHAMP BLINDMATE .50 SERIES I									
			108-1548															
			APPLICATION SPEC			114-6061			SIZE		CAGE CODE		DRAWING NO					
			MATERIAL			FINISH			WEIGHT			A3		00779		C-5084487		
			 			CUSTOMER DRAWING			SCALE		2:1		SHEET		OF		REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5084487-2](#)