




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECO-17-008763	22JAN2018	RG	SH



- 1 NUMBER "n" IS COUNTED FROM DATUM
(CIRCUIT NO.1 IS "AMP" MARK SIDE.)
- ② MATERIA: HOUSING, 66 NYLON (GF) UL 94V-0, BLACK.
: CONTACT, PHOSPHOR BRONZE.
: RETENTION LEG; BRASS.
- ③ FINISH: CONTACT; Au AT CONTACT AREA (SEE TABLE), TIN AT TINE, OVER Ni.
RETENTION LEG; TIN UNDER Ni.

OBSOLETE	6—	2			130	64	81.28	89.62	88.68	92.48	
OBSOLETE	6—	1			120	59	74.93	83.27	82.33	86.13	
	6—	0			100	49	62.23	70.57	69.63	73.43	
	5—	9			80	39	49.53	57.87	56.93	60.73	
	5—	8			68	33	41.91	50.25	49.31	53.11	
	5—	7			60	29	36.83	45.17	44.23	48.03	
	5—	6			50	24	30.48	38.82	37.88	41.68	
	5—	5			40	19	24.13	32.47	31.53	35.33	
	5—	4			36	17	21.59	29.93	28.99	32.79	
	OBSOLETE	5—	3			30	14	17.78	26.12	25.18	28.98
		5—	1	0.00076		20	9	11.43	19.77	18.83	22.63
OBSOLETE	4—	2			130	64	81.28	89.62	88.68	92.48	
	4—	1			120	59	74.93	83.27	82.33	86.13	
	4—	0			100	49	62.23	70.57	69.63	73.43	
	3—	9			80	39	49.53	57.87	56.93	60.73	
	3—	8			68	33	41.91	50.25	49.31	53.11	
	3—	7			60	29	36.83	45.17	44.23	48.03	
	3—	6			50	24	30.48	38.82	37.88	41.68	
	3—	5			40	19	24.13	32.47	31.53	35.33	
	OBSOLETE	3—	4			36	17	21.59	29.93	28.99	32.79
		3—	3			30	14	17.78	26.12	25.18	28.98
	3—	1	0.0005		20	9	11.43	19.77	18.83	22.63	
OBSOLETE	1—	2			130	64	81.28	89.62	88.68	92.48	
	1—	1			120	59	74.93	83.27	82.33	86.13	
	1—	0			100	49	62.23	70.57	69.63	73.43	
	OBSOLETE		9			80	39	49.53	57.87	56.93	60.73
		8			68	33	41.91	50.25	49.31	53.11	
		7			60	29	36.83	45.17	44.23	48.03	
	OBSOLETE		6			50	24	30.48	38.82	37.88	41.68
OBSOLETE		5			40	19	24.13	32.47	31.53	35.33	
		4			36	17	21.59	29.93	28.99	32.79	
		3			30	14	17.78	26.12	25.18	28.98	
	5175472-1		0.0002		20	9	11.43	19.77	18.83	22.63	
	PART NO.		Au PLATE		POS.	n	A	B	C	D	

LEAD FREE

GENERAL TOLERANCE

10 ≥ : ±0.2
30 ≥ > 10: ±0.25
100 ≥ > 30: ±0.3
ANGLES: ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Julyee Zhu 18AUG2004 CHK Steven Yao 18AUG2004 APVD Ikuro Enomoto 18AUG2004		 TE Connectivity Ltd.	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME AMP CHAMP .050 CONNECTOR (B-T-B) PLUG CONNECTOR (HORIZONTAL WITH RETENTION LEG)	
MATERIAL 		FINISH 		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
		WEIGHT 0.000000		A2 00779 C-5175472	
CUSTOMER DRAWING				SCALE NTS SHEET 1 of 1 REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-5175472-6](#)