


4

3


2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		S1	REVISED PER ECO-15-008427	08JUN15	JR	DH



- 1 MATES WITH .032±.001x.250 TAB
- 2 WIRE STRIP LENGTH .281
- 3 INSULATION SIZE .135 MAX DIA
- 4 CONTINUOUS STRIP ON REELS
- 5 DIMENSION DOES NOT INCLUDE TRIM BURR
- 6 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA

STANDARD	HOUSING:NYLON,COLOR-BLACK TRANSLUCENT RECEPTACLE:BRASS, TIN		9-520183-2		
BULK	HOUSING:NYLON,COLOR-RED TRANSLUCENT RECEPTACLE:BRASS, TIN		5-520183-2		
STANDARD	HOUSING:NYLON,COLOR-RED TRANSLUCENT RECEPTACLE:#3 HARD PH BRONZE, TIN		2-520183-4		
	HOUSING:NYLON,COLOR-RED TRANSLUCENT RECEPTACLE:BRASS, TIN		2-520183-2		
PACKAGING	MATERIAL & FINISH			PART NO	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P FORTNEY 10/18/88	 TE Connectivity		
		CHK JR RUTH 10/18/88			
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .015 4 PLC ± - ANGLES ± -	APVD K RANDOLPH 10/21/88	NAME		
		PRODUCT SPEC 108-2043	RECEPTACLE ASSY,ULTRA-FAST, .250 SERIES,22-18 AWG -		
		APPLICATION SPEC 114-2123			
		WEIGHT -			
MATERIAL SEE TABLE		FINISH SEE TABLE	SIZE A3	CAGE CODE 00779	DRAWING NO C-520183
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1	REV S1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-520183-1](#)