



SPECIFICATION CONTROL DRAWING				SCD		55A0841	
Title FOUR CONDUCTOR CABLE, UNSHIELDED, UNJACKETED, GENERAL PURPOSE, 600 VOLT				Date 1-13-17		Revision D	
This specification sheet forms a part of the latest issue of Raychem Specification 55A.							
<div>COMPONENT WIRES - 55A0811</div> 							
CABLE CONSTRUCTION DETAILS							
PART NUMBER 1/	CONDUCTOR SIZE (AWG)	OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lbs/1000 ft.)			
		NOMINAL	MAXIMUM				
55A0841-26-*	26	.097	.115	6.9			
55A0841-24-*	24	.109	.128	9.4			
55A0841-22-*	22	.121	.142	13.1			
55A0841-20-*	20	.140	.164	19.2			
55A0841-18-*	18	.169	.199	29.4			
55A0841-16-*	16	.186	.218	36.7			
55A0841-14-*	14	.227	.265	56.3			
55A0841-12-*	12	.269	.311	83.6			
55A0841-10-*	10	.324	.377	132.			
55A0841-8-*	8	.472	.554	246.			
55A0841-6-*	6	.583	.685	386.			
55A0841-4-*	4	.750	.874	612.			
CABLE RATINGS AND ADDITIONAL REQUIREMENTS							
TEMPERATURE RATING: 150°C Maximum continuous conductor temperature VOLTAGE RATING: 600 volts (rms) at sea level DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz INSULATION FLAWS: Spark Test, 5.7 kV (rms) at 3 kHz Impulse Dielectric Test, 8.0 kV (peak)				1/ PART NUMBER: The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors. Colors shown do not necessarily reflect the sequence of manufacturing. Example: AWG 22, orange, green, blue, and white component wires: 55A0841-22-3/5/6/9			
NOTE: Nominal values are for information only. Nominal values are not requirements.							
Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.							
1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.							
Page 1 of 1	Raychem, TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks.			 <div>Raychem Wire &amp; Cable 501 Oakside Avenue Redwood City, CA 94063-3800 Phone: 1-800-522-6752 Fax: 1-650-361-6297</div>			
	DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL						
	THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.						

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## TE Connectivity:

[55A0841-22-3/5/6/9CS2275](#) [55A0841-16-MST4CS2275](#) [55A0841-20-MAS4CS2175](#) [55A0841-16-3/5/6/9CS2275](#)  
[55A0841-20-3/5/6/9](#) [55A1111-20-9-9-5CF/1](#) [55A1111-12-9-9-F871](#) [55A1111-22-9-0-F871](#) [55A0841-16-3/5/6/9](#)  
[55A1111-14-9-9-2KF](#) [55A1111-16-9-96CS2813](#) [55A1111-24-9-9-F871](#) [55A1111-20-2-2-F871](#)