




11FEB2016 WITH R NAYAK	 TE Connectivity			
6MAR2016 HIK J K				
6MAR2016 NANTH S	NAME AMPMODU 2mm SHROUDED HEADER DUAL ROW,VERTICAL,SMD			
SPEC -64040				
ON SPEC 64040	SIZE A2	CAGE CODE 00779	DRAWING NO C=2823367	RESTRICTED TO -
ER DRAWING			SCALE 8:1	SHEET 1 OF 3
			REV A1	



1- -6 AS SHOWN

CAP	3
POST	2
HOUSING	1
DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11FEB2016 RAKSHITH R NAYAK CHK 03MAR2016 KARTHIK J K APVD 06MAR2016 PRASHANTH S PRODUCT SPEC 108-64040 APPLICATION SPEC 114-64040 WEIGHT CUSTOMER DRAWING		 TE Connectivity NAME AMPMODU 2mm SHROUDED HEADER DUAL ROW,VERTICAL,SMD -	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.1 2 PLC ±0.05 3 PLC ±- 4 PLC ±- ANGLES ±2° FINISH		SIZE A2	
MATERIAL SEE NOTES -		SEE NOTES -		CAGE CODE 00779	
				DRAWING NO C=2823367	
				RESTRICTED TO -	
				SCALE 8:1	
				SHEET 1 of 3	
				REV A1	

4

3

2

1

© 2023 TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

SMART PART NUMBER

2MM - HSD - D - VS - 00 - - -

PRODUCT SERIES

2MM

AMPMODU 2mm series

GENDER / TYPE

HSD

Shrouded headers for detent latch

NUMBER OF ROWS

D

Double row

NUMBER OF PINS PER ROW

XX

02 through 16,20,22,25
(enter two digits)

ORIENTATION & TERMINATION

VS

Vertical surface mount

PACKAGING

TBP

Tube with cap

TRP

Tape and reel with cap

PLATING

T	Tin
F	0.1µm selective Gold (Gold flash)
M	0.38µm selective Gold
H	0.76µm selective Gold

TAIL LENGTH

00

N/A for surface mount

SMART PN EXAMPLES :

1. AMPMODU 2MM, SHROUDED HEADER STD VERSION, DOUBLE ROW , 03 POSITION PER ROW , SURFACE MOUNT, TAIL LENGTH NOT APPLICABLE, TIN PLATING, TUBE WITH CAP
2MM-HSD-D03-VS-00-T-TBP

2. AMPMODU 2MM, SHROUDED HEADER STD VERSION, DOUBLE ROW , 16 POSITION PER ROW , SURFACE MOUNT, TAIL LENGTH NOT APPLICABLE, 0.76µm SELECTIVE GOLD PLATING, TAPE AND REEL WITH CAP
2MM-HSD-D25-VS-00-H-TRP

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

SEE NOTES

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC±

1 PLC±0.1

2 PLC±0.05

3 PLC±

4 PLC±

ANGLES±°

FINISH

SEE NOTES

-

DWN11FEB2016
RAKSHITH R NAYAK

CHK6MAR2016
KARTHIK J K

APVD6MAR2016
PRASHANTH S

PRODUCT SPEC108-64040

APPLICATION SPEC114-64040

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

NAME

AMPMODU 2mm SHROUDED HEADER
DUAL ROW,VERTICAL,SMD

SIZE

A2

CAGE CODE

100779

DRAWING NO

©=2823367

RESTRICTED TO

-

SCALE

1:1

SHEET

2

OF

3

REV

A1

1471-9 (3/13)

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2823908-4](#) [2823910-6](#) [2823368-4](#)