

SPECIFICATION CONTROL DRAWING

55PC0231


TITLE THREE CONDUCTOR CABLE, UNSHIELDED, UNJACKETED, 600 VOLT

Date 4-10-98

Revision D

This specification sheet forms a part of the latest issue of Raychem Specification 55PC.

COMPONENT WIRES - 55PC0211



CONSTRUCTION DETAILS						
PART NUMBER	CONDUCTOR SIZE (AWG)	DIAMETER (in.)			WEIGHT (lbs/1000 ft.)	
		LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT
55PC0231-24-*	24	.081	.085	.089	6.02	6.30
55PC0231-22-*	22	.094	.098	.102	8.82	9.13
55PC0231-20-*	20	.112	.116	.121	13.32	13.68
55PC0231-18-*	18	.132	.137	.142	20.04	20.66
55PC0231-16-*	16	.148	.153	.158	25.46	26.13
55PC0231-14-*	14	.180	.185	.191	39.17	40.06
55PC0231-12-*	12	.219	.226	.232	60.01	61.19
55PC0231-10-*	10	.269	.278	.287	94.65	96.77
55PC0231- 8-*	8	.408	.423	.438	173.	181.
55PC0231- 6-*	6	.504	.523	.542	273.	286.
55PC0231- 4-*	4	.648	.672	.696	444.	464.
55PC0231- 2-*	2	.799	.827	.858	695.	724.

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C
 Maximum continuous conductor temperature
 VOLTAGE RATING: 600 volts (rms)
 INSULATION FLAWS:
 Impulse Dielectric Test, 8.0 kV (peak)

PART NUMBER:
 The "*" in the part numbers above shall be replaced by a color code designator with a slash separating the component wire colors.
 Example: AWG 22, white, black and red component wires; 55PC0231-22-9/0/2

COLOR AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HERIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

Raychem

Raychem Corporation
 300 Constitution Drive, Menlo Park, California 94025
 1-800-2 Raychem Fax: 1-650-361-6250

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

[55PC0231-14-3/6/9](#) [55PC0231-8-3/6/9CS2602](#) [55PC0231-18-2/4/6CS2502](#) [55PC0231-20-3/6/9CS2602](#) [55PC0231-12-2/4/6CS2970](#) [55PC0231-10-3/6/9CS2602](#) [55PC0231-12-3/6/9](#) [55PC0231-16-2/4/6CS2970](#) [55PC0231-14-2/4/6CS2502](#) [55PC0231-22-2/4/6CS2970](#) [55PC0231-22-3/6/9CS2602](#) [55PC0231-24-0/4/9](#) [55PC0231-22-3/6/9](#) [55PC0231-20-2/4/6CS2970](#) [55PC0231-8-2/4/6](#) [55PC0231-12-2/4/6CS2502](#) [55PC0231-20-3/6/9](#) [55PC0231-16-9/93/96](#) [55PC0231-14-2/4/6CS2970](#) [55PC0231-16-2/4/6CS2502](#) [55PC0231-14-3/6/9CS2602](#) [55PC0231-20-9/93/96](#) [55PC0231-16-2/4/6-F940](#) [55PC0231-2-3/6/9CS2602](#) [55PC0231-10-3/6/9](#) [55PC0231-18-2/4/6CS2970](#) [55PC0231-16-3/6/9](#) [55PC0231-22-9/93/96](#) [55PC0231-22-2/4/6](#) [55PC0231-20-2/4/6CS2502](#) [55PC0231-22-2/4/6CS2780](#) [55PC0231-22-9/93/96CS2666](#) [55PC0231-16-3/6/9CS2602](#) [55PC0231-14-2/4/6-F940](#) [55PC0231-8-3/6/9](#) [55PC0231-18-3/6/9](#) [55PC0231-18-3/6/9CS2602](#) [55PC0231-12-2/4/6-F940](#)