


SPECIFICATION CONTROL DRAWING

55PC2131TITLE
THREE CONDUCTOR CABLE, FLAT BRAID SHIELDED, JACKETED, 600 VOLTDate
11-13-95Revision
E

This specification sheet forms a part of the latest issue of Raychem Specification 55PC.



CONSTRUCTION DETAILS

PART NUMBER	CONDUCTOR SIZE (AWG)	SHIELD STRAND THICKNESS (± .0004)	JACKET THICKNESS (in.)		DIAMETER (in.)			WEIGHT (lbs/1000 ft.)	
			LOWER SPEC LIMIT	TARGET WALL	LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT
55PC2131-24-*	24	.0015	.0060	.0080	.095	.100	.105	8.89	9.45
55PC2131-22-*	22	.0015	.0060	.0080	.108	.113	.118	12.09	12.72
55PC2131-20-*	20	.0015	.0065	.0085	.126	.131	.136	17.21	17.95
55PC2131-18-*	18	.0015	.0065	.0085	.146	.152	.157	24.62	25.60
55PC2131-16-*	16	.0015	.0070	.0085	.161	.168	.175	30.67	31.93
55PC2131-14-*	14	.0015	.0070	.0090	.194	.200	.206	45.38	46.79
55PC2131-12-*	12	.0015	.0070	.0090	.235	.241	.248	67.69	69.54
55PC2131-10-*	10	.0015	.0075	.0095	.291	.299	.308	105.40	108.12

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms)

DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)

JACKET FLAWS:

Spark Test, 1000 volts (rms), 60 Hz, 100% test

Impulse Dielectric Test, 6.0 kV (peak), 100 % test

SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND TEST (POST ENVIRONMENTAL):

1000 volts (rms), 60 Hz, 1 minute

PART NUMBER:

The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

Example: AWG 22, red, blue and yellow component wires; white jacket: 55PC2131-22-2/6/4-9

COLOR AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681.

RaychemRaychem Corporation
300 Constitution Drive, Menlo Park, California 94025
1-800-2 Raychem Fax: 1-415-361-6297

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55PC2131-22-MST3-9CS2743](#) [55PC2131-24-3/6/9-9CS2675](#)