



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	OO		A	ECO-06-000585	09AUG06	BSV	MZ

D

C

B

A



SPECIFICATIONS:





CURRENT RATING-0.4VA MAX., 20V MAX. (AC/DC).

INITIAL CONTACT RESISTANCE-20MILLIOHMS MAX.
@100mV & 1mA.


VOLTAGE WITHSTANDING-1000VAC BETWEEN
TREMINALS I & CASE GROUND FOR 1 MINUTE.

NOTES

1 ACTUAL DISTANCE OF CL FROM PCB WHEN MOUNTED.



(*)	BUTTON COLORS AVAILABLE
(0)	BLACK
(2)	RED
(6)	BLUE



NO CENTER TERMINAL ON "C" FUNCTION SWITCH

TPB11FG-RA-ES**	2-1	2-3(MOM)
TPB11CGRA-ES**	OFF	3-1(MOM)

SWITCH MODEL	FLAT	FLAT

TERMINAL CONNECTED WITH BUTTON
IN POSITION SHOWN.

NOTE:TERMINAL DESIGNATION NUMBERS
ARE FOR REFERENCE ONLY AND DO
NOT.APPEAR ON SWITCHES.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V.J.NARTINI 05DEC80		tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608				
		CHK R.D 08DEC80						
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PUSHBUTTON SWITCH (TPB11 *G-RA-ES*)				
		0 PLC ± -						
		1 PLC ± -						
		2 PLC ± -		SIZE CAGE CODE DRAWING NO RESTRICTED TO				
		3 PLC ± .01						
		4 PLC ± -		A200779C=6-1437571-2- - -				
		ANGLES ± 1°						
MATERIAL		FINISH		WEIGHT				
-		-		-				
CUSTOMER DRAWING				SCALE 3:1		SHEET 1 OF 1		REV A

D

C

B

A

6-1437571-2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TPB11CGRAES2](#)