





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
GE	00		C2	REVISED PER ECO-11-005030	11MAR11	RK HMR



1. FINISH : PLATE 0.000100-0.000200 THK TIN IN LOCALIZED TIN PLATE AREA, ALL OVER 0.000040-0.000080 THK NICKEL.
2. CONTACT WILL BE LUBED WITH LUBRICANT PER P/N 22014-4.
3. WIRE RANGE: 20-18 AWG WITH INSULATION DIAMETERS OF 0.089 - 0.131 INCHES.
4. PLATE 0.000030 MIN THK SELECT GOLD IN LOCALIZED PLATE AREA.



1	776349-3
1 4	776349-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. YEAGER	22FEB00	 TE Connectivity					
		CHK W. LONG	22FEB00						
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD W. LONG	22FEB00	NAME PIN CONTACT — —					
	0 PLC ± —	PRODUCT SPEC	—						
	1 PLC ± —	APPLICATION SPEC	—						
	2 PLC ± .02								
	3 PLC ± .005	—	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
	4 PLC ± —								
	ANGLES ± —								
MATERIAL 0.014 THK.CU.ALLOY	FINISH —	WEIGHT —	A2	00779	C=776349	—			
CUSTOMER DRAWING				SCALE	10:1	SHEET	1 of 1	REV	C2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[776349-1](#) [776349-3](#) [776349-3 \(Loose Piece\)](#)