

A

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , -
© COPYRIGHT - By -	ALL RIGHTS RESERVED.	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—





SELECT LOAD CHART

OBSOLETE	9,10	1-8	1-8	9,10	9,10	-	1-8	-	-	10	SSB7N2030	5-1546963-8
	1-8	9,10	-	-	2,5,6,10	-	1,7	-	-	10	SSB7N2025	4-1546963-3
	ALL	ALL	2,3,4	-	-	-	-	-	-	7	SSB7N2019	3-1546963-8
	ALL	ALL	3,4	-	-	-	-	-	-	7	SSB7N2017	3-1546963-2
	-	-	ALL	-	-	-	2,4	-	-	6	SSB7N2016	3-1546963-1
	-	1,3,5,7	-	-	1	-	-	-	-	4	SSB7CG04032224	4-1546963-9
	.250 QC TAB 90° BEND SGL SIDED (10)	.250 QC TAB 90° BEND DBL SIDED (9)	.250 QC TAB STRAIGHT DBL SIDED (8)	.250 QC TAB STRAIGHT SGL SIDED (7)	.250 QC TAB 45° BEND SGL SIDED (6)	.187 QC TAB STRAIGHT SGL SIDED (5)	.250 QC TAB 45° BEND DBL SIDED (4)	.187 QC TAB 45° BEND SGL SIDED (3)	.187 QC TAB 90° BEND SGL SIDED (2)	NO. OF POS.	CATALOG NUMBER	PART NUMBER
POSITIONS LOADED												







3	OBSOLETE	1.750	2.312		2			2				2			YES	3	SSB7CG030328 SPL	6 1546963 3			
	OBSOLETE	11.375	11.937												YES	25	SSB70G250301	2 1546963 5			
	OBSOLETE	10.937	11.500												YES	24	SSB70G240301	2 1546963 4			
	OBSOLETE	10.500	11.062												YES	23	SSB70G230301	2 1546963 3			
	OBSOLETE	10.062	10.625												YES	22	SSB70G220304	6 1546963 1			
	OBSOLETE	10.062	10.625												YES	22	SSB70G220301	2 1546963 2			
	OBSOLETE	9.625	10.187												YES	21	SSB70G210301	2 1546963 1			
	OBSOLETE	9.187	9.750												YES	20	SSB70G200301	2 1546963 0			
	OBSOLETE	8.750	9.312												YES	19	SSB7CG190301	1 1546963 9			
	OBSOLETE	8.313	8.875												YES	18	SSB7CG180301	1 1546963 8			
	OBSOLETE	7.875	8.437												YES	17	SSB7CG170301	1 1546963 7			
	OBSOLETE	7.437	8.000												YES	16	SSB7CG160301	1 1546963 6			
	OBSOLETE	7.000	7.562												YES	15	SSB7CG150301	1 1546963 5			
13	OBSOLETE	6.562	7.125			14						14			YES	14	SSB7N2020	3 1546963 4			
	OBSOLETE	6.562	7.125												YES	14	SSB7CG140301	7 1437415 6			
	OBSOLETE	6.125	6.687												YES	13	SSB7CG130301	1 1546963 3			
3	OBSOLETE	5.687	6.250												YES	12	SSB7CG120301	1 1546963 2			
	OBSOLETE	5.250	5.812					11	11						YES	11	SSB7CG110329	1 1546963 6			
	OBSOLETE	5.250	5.812												YES	11	SSB7CG110301	1 1546963 1			
3	OBSOLETE	4.812	5.375		2	8	8	2	2		8				YES	10	SSB7N2030	5 1546963 8			
3	OBSOLETE	4.812	5.375		2	8			4		2				NO	10	SSB7N2025	4 1546963 3			
	OBSOLETE	4.812	5.375												YES	10	SSB7CG100301	1 1546963 0			
		DIM B	DIM A	JUMPER	.250 QC TAB 90° BEND DBL SIDED ⑭	.250 QC TAB 90° BEND SGL SIDED ⑩	.250 QC TAB 90° BEND DBL SIDED ⑨	.250 QC TAB STRAIGHT DBL SIDED ⑧	.250 QC TAB STRAIGHT SGL SIDED ⑦	.250 QC TAB 45° BEND SGL SIDED ⑥	.187 QC TAB STRAIGHT SGL SIDED ⑤	.250 QC TAB 45° BEND DBL SIDED ④	.187 QC TAB 45° BEND SGL SIDED ③	.187 QC TAB 90° BEND SGL SIDED ②	SSB7 BUSHING ①	NO. OF POS.	CATALOG NUMBER	PART NUMBER			
																			QUANTITIES		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLIGEL 3/5/04		 TE Connectivity Ltd.				
		CHK S YODER 3/5/04						
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S YODER 3/5/04		NAME		
		0 PLC ± - 1 PLC ± - 2 PLC ± .02 3 PLC ± .010 4 PLC ± - ANGLES ± 3°		PRODUCT SPEC —		SSB7CGXX0301		
				APPLICATION SPEC —				
MATERIAL —		FINISH —		WEIGHT —	A2	00779	C-8-796602-0	RESTRICTED TO —
CUSTOMER DRAWING						SCALE NTS	SHEET 2 of 4	REV R1




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-






~~4-1546963-3~~ OBSOLETE





~~5-4-1546963-1~~





~~5-2-1546561-7~~





~~4-1546963-9~~ OBSOLETE




OBSOLETE ~~4-1546963-6~~



~~5-1546963-2~~ OBSOLETE



~~5-1546963-6~~ OBSOLETE



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLGE	3/5/04	 TE Connectivity Ltd.				
DIMENSIONS: INCHES		CHK S YODER	3/5/04					
		APVD S YODER	3/5/04	NAME SSB7CGXX0301				
		PRODUCT SPEC —						
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL —		WEIGHT —		A2	00779	C-8-796602-0	—	
FINISH —		CUSTOMER DRAWING				SCALE NTS	SHEET 3 of 4	REV R1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D




C

B


A



~~5-1546963-8~~ OBSOLETE



~~6-1546963-3~~ OBSOLETE



D

C

B

A

8-796602-0

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLGEL 3/5/04	TE Connectivity Ltd.							
		CHK S YODER 3/5/04								
		APVD S YODER 3/5/04	NAME							
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC						
		0 PLC ± -		SSB7CGXX0301						
		1 PLC ± -								
		2 PLC ± .02								
		3 PLC ± .010								
4 PLC ± -		4 ANGLES ± 3°		APPLICATION SPEC						
MATERIAL		FINISH		WEIGHT		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
-		-		-		A2		00779	C-8-796602-0	-
CUSTOMER DRAWING				SCALE		SHEET		REV		
				NTS		4 OF 4		R1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[SSB7CG050301](#) [SSB7CG140301](#) [SSB7CG090301](#)