



© 1972 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

REVISIONS

ZONE	LTR	DESCRIPTION	DATE	APPROVED
	01	REVISED LOCKING LANCE (ECN 1035)	8-15-75	DM
	02	REVISED LOCKING LANCE (ECN 1158)	12-3-75	DM
	03	ADDED -6 ECH 3097	3/21/77	SS
	04	REV ECN 1921	3-28-84	SS
✓	A	REV LOC (DIST AD-47)	11-21-89	BF
	B	OBS -3 PER DDIO 0976-93	1-13-94	JH/PS



1. WIRE RANGE : #26 - #30
2. INSULATION RANGE : .048 MAX DIA
3. FOR SECTIONS AND ADDITIONAL DIMENSIONS SEE AMP CUSTOMER DRAWING #85967.

OBSOLETE	86015-6	.000030 GOLD OVER .000050 NICKEL; .000100 GOLD ON CONTACT AREAS
	86015-5	GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT, .000015 GOLD IN CONTACT AREA ONLY.
	86015-4	.000050 GOLD OVER .000050 NICKEL
OBSOLETE	86015-3	BRIGHT TIN
	86015-2	GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT, .000030 GOLD IN CONTACT AREA ONLY.
	86015-1	.000030 GOLD OVER .000050 NICKEL

PART NO

FINISH

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES
TOLERANCES ON:
DECIMALS ± #
ANGLES ± #

CONTRACT NO.

AMP

AMP INCORPORATED
HARRISBURG, PENNSYLVANIA

MATERIAL
BERYLLIUM
COPPER

DR. *[Signature]* 2/24/72
APPD *[Signature]* 2/22/72
REV *[Signature]* 2/22/72
DSGN APPD
OTHER APPD

NAME
RECEPTACLE CONTACT,
MOD IV, CRIMP SNAP-IN
(LOOSE PIECE)

SIZE
B
CODE IDENT. NO.
00779

NUMBER
86015

SHEET

CUSTOMER DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[86015-5](#)