

CGPE - 105
Flexible, Commercial Grade, Polyolefin,
Heat-Shrinkable Tubing




Table 1: Dimensions mm(inches)

Size	As Supplied		Recovered							
	Inside Diameter Minimum (D)		Inside Diameter Maximum (d)		Wall Thickness (W)					
	mm	in.	mm	in.	Minimum		Maximum		Nominal	
	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
3/64	1.17	.046	0.58	.023	0.33	.013	0.48	.019	0.40	.016
1/16	1.60	.063	0.79	.031	0.35	.014	0.50	.020	0.43	.017
3/32	2.36	.093	1.17	.046	0.43	.017	0.58	.023	0.50	.020
1/8	3.17	.125	1.57	.062	0.43	.017	0.58	.023	0.50	.020
3/16	4.74	.187	2.36	.093	0.43	.017	0.58	.023	0.50	.020
1/4	6.35	.250	3.17	.125	0.56	.022	0.71	.028	0.64	.025
3/8	9.50	.375	4.74	.187	0.56	.022	0.71	.028	0.64	.025
1/2	12.70	.500	6.35	.250	0.56	.022	0.71	.028	0.64	.025
3/4	19.05	.750	9.50	.375	0.69	.027	0.84	.033	0.76	.030
1	25.40	1.000	12.70	.500	0.76	.030	1.01	.040	0.88	.035
1-1/2	38.10	1.500	19.05	.750	0.86	.034	1.17	.046	1.01	.040
2	50.80	2.000	25.40	1.000	0.96	.038	1.32	.052	1.14	.045


For More Details See CGPE - 105 Specification, TEC - 108 - 120008

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT 2017 CGPE-105

DIMENSIONS: mm	DWN	07-JUNE-17			TE Connectivity 305 Constitution Drive Menlo Park, CA 94025 USA						
	J. Bitter										
TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK	-	NAME CGPE - 105 Flexible, Commercial Grade, Polyolefin, Heat - Shrinkable Tubing								
	APVD	-									
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC	TEC-108-120008	SIZE	A4	CAGE CODE	06090	DRAWING NO	CGPE-105	RESTRICTED TO	-	
	APPLICATION SPEC	-	WEIGHT	0	CUSTOMER DRAWING		SCALE	None	SHEET	1 OF 1	REV

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[CGPE-105-3/8-0-SP](#)