




4		3		2		1	
THIS DRAWING IS UNPUBLISHED		RELEASED FOR PUBLICATION		2017		REVISIONS	
© COPYRIGHT 2017		BY -TE CONNECTIVITY		ALL RIGHTS RESERVED.		P	APVD
SEAL TYPE		CONTACT SIZE		MIN. INSUL. O.D.		MAX. INSUL. O.D.	
WIRE RANGE [mm ²] REF ONLY		L		DESCRIPTION		DATE	
NORMAL		16		REVISED PER PCN E-17-014648		20JUN2017	
E		16					



5. MATERIAL - HOUSING: PLASTIC (BLACK); GROMMET: RUBBER; INSERT: STEEL.

4. WHEN X = E: MARK LETTER "E" IDENTIFIES "E" WIRE SEAL.
WHEN X = BLANK: IDENTIFIES "NORMAL" WIRE SEAL.


3. THIS PART MATES WITH DRC16-24SBX-XXXX PLUG.
(X = WIRE SEAL ID; XXXX= ALL MODIFICATIONS)

2. FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS, SEE DRAWING 0425-015-0000.

1. RECEPTACLE IS SUPPLIED WITH DUST CAP (NOT SHOWN).

NOTES:

TE INTERNAL PN	DEUTSCH PN
DRC14-24PB	DRC14-24PB
DRC14-24PBE	DRC14-24PBE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. APOSTOL 03APR2013		TE Connectivity							
DIMENSIONS: INCHES [mm]		CHK D. HASIBUAN 03APR2013									
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. HASIBUAN 03APR2013		NAME INLINE RECEPTACLE 24 CONTACTS SIZE 16 DRC SERIES KEY ARRANGEMENT -B-							
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [.64] 4 PLC ± ANGLES ±0°30'0"		PRODUCT SPEC -									
		APPLICATION SPEC -		SIZE A3		CAGE CODE 4AFU8		DRAWING NO C=DRC14-24PBX		RESTRICTED TO -	
		WEIGHT -									
		CUSTOMER DRAWING		SCALE 1:25		SHEET 1		OF 1		REV B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[DRC14-24PB](#)