


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE PER ECO-14-012861	08-27-14	DM	DM



4. THICKNESS: 3.18 [.125]

3. PART NO. HD10-3-GKT

2. TEMPERATURE RATING: -57°C TO +107°C [-70°F TO +225°F]

1. THIS PART IS USED ON HD10-3-XXX RECEPTACLES, WHERE XXX IS PIN ARRANGEMENTS. SEE INDIVIDUAL CUSTOMER DRAWINGS

2014


RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

© COPYRIGHT 2014 BY TE CONNECTIVITY

DIMENSIONS: MM [INCH]	DWN D. MEYER 27AUG2014	MATERIAL CLD CELL SPONGE	FINISH BLACK
	CHK I. GRANTCHAROVA 27AUG2014	 TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. MEYER 27AUG2014		
0 PLC ±	PRODUCT SPEC	NAME GASKET, RECEPTACLE, SIZE 3 HD10 SERIES	
1 PLC ±	APPLICATION SPEC		
2 PLC ± 0.76 [.030]	WEIGHT .91 g	SIZE A 4	CAGE CODE 4AFU8
3 PLC ±	Customer Drawing		DRAWING NO C-HD10-3-GKT
4 PLC ±			RESTRICTED TO -
ANGLES ± 5°			SCALE NONE
		SHEET 1 OF 1	REV A



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HD10-3-GKT](#)