


LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
	D	REVISED PER E.O. P17811		24JUL2002	XS	RDR	
	E	REVISED PER E.O. P21412		20JUL2012	AM	RDR	
	F	REVISED PER ECO-14-019072		23FEB2015	JA	DM	
	F1	REVISED PER ECO-16-013285		08SEP2016	DD	DM	



5. RECEPTACLE IS SUPPLIED WITH DUST CAP (2415-001-2405).

7. PART MODIFICATION: THREADED ADAPTER

- 4 MATERIAL: RECEPTACLE HOUSING: PA66 GF10 (BLACK)
CONDUIT ADAPTER: PA66 GF10 (GREEN, GRAY, BLUE)
GROMMET: SILICONE (ORANGE-RED)

- 3 SEE 0425-021-0000 APPLICATION SPECIFICATION
A. RECOMMENDED WIRE INSULATION RANGE
B. CONTACT REMOVAL TOOLS
C. RECOMMENDED MOUNTING HOLE & PANEL THICKNESS
D. MOUNTING HARDWARE & MOUNTING TORQUE.


2. THIS RECEPTACLE MATES WITH HDP26-24-XXP/SX-XXXX PLUG
X = SEAL TYPE (N,T,E)
XX = INSERT ARRANGEMENT
XXXX = MODIFICATION

- 1 SEE CUSTOMER DRAWING, 0425-014-2400 FOR AVAILABLE INSERT ARRANGEMENTS AND PART NUMBERS.

NOTES:

- 6 CONDUIT ADAPTER ACCEPTS EITHER TYPES:
A. CONDUIT ADAPTER CAP NUT (CN21) AND SEAL RING (SRN21)
B. BACKSHELL (M902-2243) COMPRESSION NUT (M902-2053) CABLE Ø.430-.570 [10.92-14.78]
C. BACKSHELL (M902-2244) COMPRESSION NUT (M902-2054) CABLE Ø.570-710 [14.78-18.03]

- 8 DATE CODE: IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY.
YEAR: FIRST AND SECOND DIGITS. (14 = 2014)
MONTH: THRID DIGIT, EXCLUDING I. A = JAN., B = FEB., C = MARCH.... (K = OCTOBER)
DAY: FOURTH AND FIFTH DIGITS (14 = 14th DAY)
HOUR: SIXTH AND SEVENTH DIGITS (11 = 11AM)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	04SEP1997		
		CHK	19JUL2002		
		APVD	23JUL2002	NAME	
		PRODUCT SPEC	0425-021-0000	RECEPTACLE, THREADED SIZE 24, -L015 MOD HDP SERIES	
		APPLICATION SPEC	3	SIZE	
		MATERIAL	4	CAGE CODE	
		FINISH	N/A	DRAWING NO	
				RESTRICTED TO	
				A3 4AFU8	
				Customer Drawing	
				SCALE	
				2:1	
				SHEET	
				1 OF 1	
				REV	
				F1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HDP24-24-9PE-L015](#)