





THIS DRAWING IS UNPUBLISHED		RELEASED FOR PUBLICATION		2015		REVISIONS					
COPYRIGHT 1999		BY TE CONNECTIVITY		ALL RIGHTS RESERVED.		P	LTR	DESCRIPTION	DATE	DWN	APVD
							NC	NEW RELEASE PER E.O. P15416	05SEP1997	SB	RDR
							A	REVISED PER E.O. P15904	12FEB1999	RO	RDR
							B	REVISED PER E.O. P17090	22JAN2001	AR	RDR
							C	REVISED PER ECO-14-019072	23FEB2015	JA	DM



6. PART MODIFICATION: THREADED ADAPTER
5. CONDUIT ADAPTER ACCEPTS EITHER TYPES:
A. CONDUIT ADAPTER CAP NUT (CN21) AND SEAL RING (SRN21)
B. BACKSHELL (M902-2243), COMPRESSION NUT (M902-2053), CABLE Ø.430-.570 [10.92-14.78]
C. BACKSHELL (M902-2244), COMPRESSION NUT (M902-2054), CABLE Ø.570-710 [14.78-18.03]
4. MATERIAL: PLUG HOUSING/COUPLING RING: PA66 GF10 (BLACK)
CONDUIT ADAPTER: PA66 GF10 (GREEN, GRAY, BLUE)
GROMMET: SILICONE (ORANGE-RED)
3. SEE 0425-021-0000 APPLICATION SPECIFICATION
A. RECOMMENDED WIRE INSULATION RANGE
B. CONTACT REMOVAL TOOLS

2. THIS PLUG MATES WITH HDP24-24XXP/SX-XXXX RECEPTACLE
X = SEAL TYPE (N,T,E)
XX = INSERT ARRANGEMENT
XXXX = MODIFICATION

1. SEE CUSTOMER DRAWING 0425-014-2400 FOR AVAILABLE INSERT ARRANGEMENTS AND PART NUMBERS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	19JAN1999	TE TE Connectivity	
		CHK	15JAN2001		
		APVD	15JAN2001		
		PRODUCT SPEC	0425-021-0000		
DIMENSIONS: INCHES[mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PLUG, COUPLING RING SIZE 24, -L015 MOD HDP SERIES	
		0 PLC	±	SIZE	
		1 PLC	±	CAGE CODE	
		2 PLC	±	DRAWING NO	
		3 PLC	±.015 [0.38]	RESTRICTED TO	
		4 PLC	±	A3 4AFU8	
		ANGLES	±0°30'0"	C-HDP26-24-XXP/SX-L015	
MATERIAL		FINISH	N/A	SCALE	
4				2:1	
				SHEET 1 OF 1	
				REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HDP26-24-16PN-L015](#)