


4

3

2


1

| REVISIONS | | | | | | |
|-----------|-----|-------------------------|--|--|--------------|----------|
| ZONE | LTR | DESCRIPTION | | | DATE | APPROVED |
| — | A | CHG'D PER DCO * T-02582 | | | W.J. 4-23-81 | Ans |



Raychem
PART NO.
MTC100-JAI-SII-T06

DATE CODE



5 WEIGHT (MAX.) 8 LBS. GRAMS
0054 2.46

4 SOCKET ONE: SOCKET NUMBER ONE MARKED IN CONTRASTING COLOR.

3. WAFER: WAFER MEETS THE REQUIREMENTS OF RAYCHEM SPECIFICATION D-6012.

2. FINISH: 2-A SOCKET WAFER; FINISH TO BE AS MOLDED.
2-B SOCKET CONTACT; GOLD PLATE PER MIL-G-45204 CLASS I.
2-C CONTACT TAIL; COATED WITH SOLDER PER QQ-S-571.

1. MATERIAL: 1-A SOCKET WAFER; HIGH GRADE POLYARYLENE THERMO-PLASTIC.
1-B SOCKET CONTACT; COPPER ALLOY PER QQ-B-750 (A).
1-C SOLDERPAK® TERMINATORS ASSY; REFER TO RAYCHEM DWG. CTA-0035 FOR DATA.

NOTES

If this document is printed it becomes uncontrolled.
Check with the web for latest revision.

DO NOT SCALE THIS DRAWING

SPECIFICATION CONTROL DRAWING

© Raychem Corporation 1981

| | | | | | |
|--|----------|--------|---------|--|--------------------|
| UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES BRACKETED DIMENSIONS () ARE METRIC AND TOLERANCES ARE: .XXX: ± .005 (0.13 M.M.) .XX: ± .02 (0.51 M.M.) Δ: ± — | DRAWN | W.V.J. | 1-15-81 | Raychem <small>RAYCHEM CORPORATION 300 CONSTITUTION DRIVE MENLO PARK, CALIFORNIA 94025</small> | |
| | CHECKED | | | | |
| | APPROVED | | | TITLE KIT, 1" SOCKET WAFER "A" WITH SOLDERPAK® TERMINATORS, FOR ROUND WIRE (20-26AWG), 125 °C TEMPERATURE RATING MTC 100 SERIES | |
| | APPROVED | | | | |
| | APPROVED | | | SIZE | CODE IDENT |
| | | | | C | NO. 06090 |
| | | | | DWG. NO. | MTC100-JAI-SII-T06 |
| | | | | WEIGHT | 5 |
| | | | | SHEET | 1 OF 1 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[MTC100-JA1-S11-T06](#)