





If this document is printed it becomes uncontrolled.
Check with the web for latest revision.

REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
B	REVISED PER ECN	T-19966	03/29/95 HAGMANN



NOTES:

1. MATERIAL: 1 - A. WAFER; INSERT MATERIAL, HIGH GRADE BLACK POLYARYLENE THERMOPLASTIC.
1 - B. CONTACT: COPPER ALLOY PER QQ-B-613.
1 - C. INTERFACIAL SEAL; SILICONE ELASTOMER PER ZZ-R-765.
2. FINISH: 2 - A. WAFER; FINISH TO BE AS MOLDED.
2 - B. CONTACT; ENGAGING END, GOLD PLATED PER MIL-G-45204, CLASS 1 TERMINATION END, SOLDER COATED PER QQ-S-571.
3. SPECIAL NOTES 3 - A. THIS PART IS DESIGNED TO MEET THE REQUIREMENTS OF **Raychem** SPECIFICATION C-6111. QUALIFICATION IS PENDING.
4. THIS INSERT IS INTENDED FOR USE WITH THE MTC100 2" CONNECTOR HOUSING.

TABLE 1

SPECIAL TEST REQUIREMENTS	
EXAMINATION OR TEST	REQUIREMENT
VISUAL AND DIMENSIONAL EXAMINATION	PER SCD
INSULATION RESISTANCE AT AMBIENT TEMPERATURE	5000 MEGOHMS MINIMUM
DIELECTRIC WITHSTAND VOLTAGE AT SEA LEVEL	1500 VAC (RMS) 60 HZ

DO NOT SCALE THIS DRAWING

SPECIFICATION CONTROL DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND TOLERANCES ARE XXX = +/- .005 (0.13 MM) XX = +/- .02 (0.51 MM)	DRAWN	LOVATO	7-29-92	Raychem RAYCHEM CORPORATION 300 CONSTITUTION MENLO PARK, CALIFORNIA 94025			
	CHECKED			TITLE WAFER, PIN, "B2" 4-WAY, 125 C, 20-26 AWG FOR MTC100 CONNECTORS			
	APPROVED						
MATERIAL NOTES	APPROVED			SIZE A CODE IDENT 06090 DWG NO MTC100-YB1-025			
	APPROVED						
FINISH NOTES	CAD NAME	008260-1.PCX		SCALE WEIGHT 1.72 G. MAX SHEET 1 OF 1			
	PCN	630328-000					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[630328-000](#)