





UNRESTRICTED
COILED DIMENSIONS



UNCOILED DIMENSION

REVISIONS

LTR	DESCRIPTION	DATE
A	INITIAL RELEASE PER ECO-10-024943	12/06/2010
B	REVISED PER ECO-11-011297	05/03/2011

NOTES:



1. MATERIAL: SILICONE ELASTOMER PER RT-1140
2. COLOR: BLACK
3. OPERATING TEMPERATURE RANGE: -75°C to +180°C
4. TRIMMING MAY BE REQUIRED.
5. NUMBER OF WRAPS WILL VARY FOR EACH SIZE.
6. MARKING: EACH PART SHALL BE STAMPED WITH PART DESCRIPTION IN WHITE INK.

TABLE OF DIMENSIONS

PART DESCRIPTION	E REF	D REF	H ± 10%	L ± 10%	W ± 10%	BUNDLE O.D. MIN
SEB-A	.34 [8,6]	.34 [8,6]	.40 [10,2]	1.00 [25,4]	.06 [1,5]	.05 [1,3]
SEB-B	.46 [11,7]	.46 [11,7]	.40 [10,2]	2.00 [50,8]	.06 [1,5]	.05 [1,3]
SEB-C	.53 [13,5]	.53 [13,5]	.50 [12,7]	3.00 [76,2]	.06 [1,5]	.05 [1,3]
SEB-D	.62 [15,7]	.62 [15,7]	.60 [15,2]	4.00 [101,6]	.06 [1,5]	.10 [2,5]
SEB-E	.75 [19,1]	.75 [19,1]	.60 [15,2]	6.00 [152,4]	.06 [1,5]	.30 [7,6]
SEB-F	.87 [22,1]	.87 [22,1]	.60 [15,2]	9.00 [228,6]	.06 [1,5]	.30 [7,6]

If this document is printed it becomes uncontrolled. Check for the latest revision

Raychem Molded Parts
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE INCHES. METRIC DIMENSIONS ARE IN BRACKETS.		PREPARED BY: M. MAZARIEGOS		 TE Connectivity	
DECIMAL TOLERANCES .XXX ± 0.005 [0.13 mm] .XX ± 0.01 [0.25 mm] .X ± 0.1 [0.50 mm]		APPROVED BY: DHURRELL			
ANGLE TOLERANCE .X ± 10 DEG.				TITLE SIDE ENTRY BUSHING	
TYCO ELECTRONICS RESERVES THE RIGHT TO AMEND THIS DRAWING AT ANY TIME. USERS SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.				SIZE B	CODE IDENT. NO. 06090
© 2011 Tyco Electronics Corporation. All rights reserved.				DO NOT SCALE THIS DRAWING	
				SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[SEB-A](#)