



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	6	RELEASED AS PER ECO-17-009529	03JUL2017	PV	MP

a) Part as supplied.



b) Part after unrestricted recovery.



NOTES:

TCFS-XX-XXX-0XX-25CH

Thread Length (20mm standard) (±5mm increments)

Feedthrough Material/Finish

19B Aluminium alloy plated cadmium olive drab over electroless nickel

19C Aluminium alloy plated electroless nickel

19Q Aluminium alloy plated zinc cobalt over electroless nickel

62C Stainless steel plated electroless nickel

Feedthrough Size

Moulded Part Material: -25C (Black); Elastomer/Silver Composites, Fluid Resistant

Kits to include cleaning tissue, 1 piece 100 grit emery cloth & 1 piece of atom.

Kit to be used in conjunction with TCFS installation procedure.

Dimensions in mm [inches for reference]

Part No.	A MIN	J		M THREAD	A/F NUT	L NOM	P ±10% b	JO REF b
		MIN a	MAX b					
TCFS-12	7.4 [.29]	8 [.31]	5.0 [.20]	M12 X 1.5	17 [.67]	24 [.94]	50 [1.97]	15 [.59]
TCFS-16	10.1 [.40]	13 [.51]	6.0 [.24]	M16 X 1.5	22 [.87]	29 [1.14]	65 [2.56]	17 [.67]
TCFS-20	14.1 [.56]	15 [.59]	7.2 [.28]	M20 X 1.5	27 [1.06]	34 [1.34]	77 [3.03]	20 [.79]
TCFS-24	19.1 [.75]	19 [.75]	8.5 [.33]	M24 X 1.5	30 [1.18]	38 [1.50]	90 [3.54]	25 [.98]
TCFS-30	24.1 [.95]	24 [.94]	10.0 [.39]	M30 X 1.5	36 [1.42]	47 [1.85]	115 [4.53]	30 [1.18]
TCFS-36	30.1 [1.19]	33 [1.30]	15.8 [.62]	M36 X 1.5	41 [1.61]	52 [2.05]	140 [5.51]	30 [1.18]

DIMENSIONS:

mm [INCHES]

DWN

P. VU

17OCT2016

MATERIAL

SEE NOTES

FINISH

SEE NOTES

CHK

N. NAGAR

17OCT2016

APVD

M. POPE

17OCT2016

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

CUSTOMER DRAWING

NAME

ADAPTOR ASSEMBLY

SIZE

A4

CAGE CODE

00779

DRAWING NO

C-TCFS-XX-XXX-0XX-25CH

RESTRICTED TO


SCALE

DNS

SHEET

1 OF 1

REV 6



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TCFS-36-62C-020-25CH](#)