

## SST/SST-FR

### Self-Sealing, Heat-Shrinkable Tubing

#### Product Facts

- Thick adhesive liner forms an effective barrier against fluids and moisture
- Thick-wall insulation, strain relief and abrasion protection
- No need for greases, tape, or epoxy
- Expansion ratios as high as 3:1
- Available in flame-retardant material
- SST has the following agency approvals:
  - ABS (American Bureau of Shipping)
  - Lloyd's (Lloyd's Register of Shipping)
- RoHS compliant



#### Applications

SST provides a simple, positive splice-sealing method that offers protection under adverse environmental conditions. Tubing supplied with standard sealant provides water sealing and environmental protection in wet or underground applications. The thermoplastic adhesive not only seals, but also provides mechanical strain

relief. The polymer tubing has excellent insulating, abrasion-resistance, and strain-relief properties.

#### Installation

Minimum shrink temperature: 90°C [195°F]  
 Minimum full recovery temperature: 121°C [250°F]

#### Operating Temperature Range

-55°C to 110°C  
 [-67°F to 230°F]

### Specifications/Approvals

Series	Military	Industry	Agency	Raychem
SST	—	—		RW-2011
SST-FR	AMS-DTL-23053/15*, Classes 1 and 2	ASTM D 685, nonburning	ABS, Lloyd's	RW-2011

\*Formerly MIL-I-23053/15 and MIL-DTL-23053/15.

Available in:	Americas	Europe	Asia Pacific
	■	■	■



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## TE Connectivity:

[SST-48-11/226-CS8747](#) [SST-48-04/FR/97/NM](#) [SST-48-15/FR/YLW/97](#) [SST-12-07/97](#) [SST-12-27/226](#) [SST-24-27/FR/97/NM](#) [SST-48-40/FR/97/NM](#) [SST-48-13/226/NM](#) [SST-27-20/FR/WHT/97](#) [SST-9-07/226](#) [SST-6-07/226](#) [SST-9-11/FR/97](#) [SST-48-13/FR/97-CS8407](#) [SST-9-27/FR/97](#) [SST-12-13/97](#) [SST-9-27/FR/WHT/97](#) [SST-9-15/FR/97/NM](#) [SST-48-04/FR/97-CS8407](#) [SST-48-11/97/NM](#) [SST-48-07/RED/97/NM](#) [SST-48-17/226/NM](#) [SST-12-17/97](#) [SST-9-27/FR/RED/97](#) [SST-48-45/FR/97](#) [SST-6-07/97](#) [SST-9-20/FR/97/NM](#) [SST-9-27/FR/97/NM](#) [SST-12-20/97](#) [SST-30-04/CL/226](#) [SST-48-27/FR/WHT/97](#) [SST-48-11/FR/YLW/97/NM](#) [SST-48-17/226-CS8748](#) [SST-48-20/RED/226/NM](#) [SST-48-30/RED/226/NM](#) [SST-48-40/RED/226/NM](#) [SST-27-20/FR/97](#) [SST-24-27/97](#)