

PUSH GRIP WIRE CONNECTORS

TE Connectivity (TE) Push Grip Wire Connectors are insulated splice connectors for electrical installations. These tool-less, poke-in wire splice connectors provide visual termination of 22 - 12 AWG solid and stranded wires. The splice is color-coded for easy identification and the compact size is designed to be used in tight spaces.



Applications

- Retrofit Lighting
- Digital Signage
- Light Commercial Building Equipment
- Residential Wiring Systems

Electrical

- Building wiring: 600 volt max.
- Lighting fixtures/ luminaries and signs: 1000 volt max.

Mechanical

- UL 486C Listed
- CSA 22.2 No. 188 Certified

Specifications

- Product Specification: [108-133070](#)
- Application Specification: [114-133071](#)
- Instruction Sheet: [408-133072](#)

Materials

- Polycarbonate, flame retardant to UL 94-V2 or UL94-V0 working temperature 110°C (IEC), 105°C/221°F (UL)
- UL 746C
- Operating Temperature: -40 to 105°C


Key Benefits

- Color coded for easy identification
- Compact in size
- Test slot for voltage testing

Product Selection Information

Part Number	PN (alias)	Description	Positions	Color
2299514-1	CS6084-000	CPGI-WC-PG-2-PORT	2	Yellow
2299515-1	CR2094-000	CPGI-WC-PG-3-PORT	3	Orange
2299516-1	CR2095-000	CPGI-WC-PG-4-PORT	4	Gray
2299517-1	CR2097-000	CPGI-WC-PG-5-PORT	5	Blue
2299518-1	CS6085-000	CPGI-WC-PG-6-PORT	6	Purple

Dimensions



te.com

© 2016 TE Connectivity Ltd. Family of Companies. All Rights Reserved. TE, TE Connectivity, and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, product and Company names mentioned herein may be trademarks of their respective owners.
1-1773884-2 JN 6/2016

USA: +1 (800) 522-6752
Canada: +1 (905) 475-6222
Mexico: +52 (0) 55-1106-0800
Latin/S. America: +54 (0) 11-4733-2200
Germany: +49 (0) 6251-133-1999

UK: +44 (0) 800-267666
France: +33 (0) 1-3420-8686
The Netherlands: +31 (0) 73-6246-999
China: +86 (0) 400-820-6015

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[CPGI-WC-PG-3-PORT-BULK](#)