

TE P/N	TE CD	Nanonics P/N	Part Description
1589058-1	1589058	QCM019SC0DC012F	Quick disconnect, circular, metal, 19 position, receptacle, 28 AWG single strand, color coded PTFE wire, 12 inches, flush mount.
1589058-2	1589058	QCM019SC0DM072F	Quick disconnect, circular, metal, 19 position, receptacle, 28 AWG solid, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 72 inches, flush mount.
1589058-3	1589058	QCM019SC2DC006F	Quick disconnect, circular, metal, 19 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, flush mount.
1589058-4	1589058	QCM019SC2DC018F	Quick disconnect, circular, metal, 19 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 18 inches, flush mount.
1589058-5	1589058	QCM019SC2DC020F	Quick disconnect, circular, metal, 19 position, receptacle, 30AWG 7 strand, color coded PTFE wire, 20 inches, flush mount.
1589058-6	1589058	QCM019SC2DMC16F	Quick disconnect, circular, metal, 19 position, receptacle, 30AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 16 centimeters, flush mount.
1589058-7	1589058	QCM019SC2DMC46F	Quick disconnect, circular, metal, 19 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 46 centimeters, flush mount.
1589058-8	1589058	QCM019SC2DXC30F	Quick disconnect, circular, metal, 19 position, receptacle, 30 AWG 7 strand, white PTFE wire, 30 centimeters, flush mount.
1-1589058-4	1589058	QCM019SC2DC180F	Quick disconnect, circular, metal, 19 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 180 inches, flush mount.
1-1589058-5	1589058	QCM019SC2DMC05F	Quick disconnect, circular, metal, 19 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 5 centimeters, flush mount.
1-1589058-6	1589058	QCM019SC2DC012F	Quick disconnect, circular, metal, 19 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 12 inches, flush mount.
1-1589058-7	1589058	QCM019SC0DM012F	Quick disconnect, circular, metal, 19 position, receptacle, 28 AWG solid, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 12 inches, flush mount.
1-1589058-8	1589058	QCM019SC2DC003F	Quick disconnect, circular, metal, 19 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 3 inches, flush mount.
1-1589058-9	1589058	QCM019SC2DC016F	Quick disconnect, circular, metal, 19 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 16 inches, flush mount.
2-1589058-0	1589058	QCM019SC2DMC40F	Quick disconnect, circular, metal, 19 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 40 centimeters, flush mount.
2-1589058-1	1589058	QCM019SC2DC024F	Quick disconnect, circular, metal, 19 position, receptacle, 30AWG 7 strand, color coded PTFE wire, 24 inches, flush mount.
2-1589058-2	1589058	QCM019SC2DM024F	Quick disconnect, circular, metal, 19 position, receptacle, 30AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 24 inches, flush mount.
2-1589058-3	1589058	QCM019SC2DMM02F	Quick disconnect, circular, metal, 19 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 2 meters, flush mount.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[QCM019SC0DM012F](#)