

| TE P/N      | TE CD   | Nanonics P/N   | Part Description                                                                                                                                                      |
|-------------|---------|----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1589064-1   | 1589064 | TCM019PC0DCC10 | Threaded coupling, circular, metal, 19 position, plug, 28 AWG solid, color coded PTFE wire, 10 centimeters.                                                           |
| 1589064-2   | 1589064 | TCM019PC0DXC10 | Threaded coupling, circular, metal, 19 position, plug, 28 AWG solid, white PTFE wire, 10 centimeters.                                                                 |
| 1589064-3   | 1589064 | TCM019PC2DC003 | Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 3 inches.                                                              |
| 1589064-4   | 1589064 | TCM019PC2DC006 | Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 6 inches.                                                              |
| 1589064-6   | 1589064 | TCM019PC2DC012 | Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches.                                                             |
| 1589064-8   | 1589064 | TCM019PC2DC024 | Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 24 inches.                                                             |
| 1589064-9   | 1589064 | TCM019PC2DC036 | Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 36 inches.                                                             |
| 1-1589064-1 | 1589064 | TCM019PC2DC066 | Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 66 inches.                                                             |
| 1-1589064-2 | 1589064 | TCM019PC2DCC30 | Threaded coupling, circular, metal, 19 position, plug, 30awg 7 strand, color coded PTFE wire, 30 centimeters.                                                         |
| 1-1589064-3 | 1589064 | TCM019PC2DM036 | Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 36 inches.      |
| 1-1589064-4 | 1589064 | TCM019PC2DC020 | Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 20 inches.                                                             |
| 1-1589064-5 | 1589064 | TCM019PC0DC036 | Threaded coupling, circular, metal, 19 position, plug, 28 AWG solid, color coded PTFE wire, 36 inches.                                                                |
| 1-1589064-6 | 1589064 | TCM019PC2DM024 | Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 24 inches.      |
| 1-1589064-7 | 1589064 | TCM019PC2DM012 | Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 12 inches.      |
| 1-1589064-8 | 1589064 | TCM019PC3DM036 | Threaded coupling, circular, metal, 19 position, plug, 32 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 36 inches.      |
| 1-1589064-9 | 1589064 | TCM019PC2DMC10 | Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 10 centimeters. |
| 2-1589064-0 | 1589064 | TCM019PC4DXC11 | Threaded coupling, circular, metal, 19 position, plug, 34 AWG 7 strand, white PTFE wire, 11 centimeters                                                               |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TCM019PC0DC036](#)