

| TE P/N      | TE CD   | Nanonics P/N   | Part Description                                                                                                                                                     |
|-------------|---------|----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1589065-1   | 1589065 | TCM044PC2DC003 | Threaded coupling, circular, metal, 44 position, plug, 30 AWG 7 strand, color coded PTFE wire, 3 inches.                                                             |
| 1589065-2   | 1589065 | TCM044PC2DC006 | Threaded coupling, circular, metal, 44 position, plug, 30 AWG 7 strand, color coded PTFE wire, 6 inches.                                                             |
| 1589065-4   | 1589065 | TCM044PC2DC012 | Threaded coupling, circular, metal, 44 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches.                                                            |
| 1589065-8   | 1589065 | TCM044PC2DC036 | Threaded coupling, circular, metal, 44 position, plug, 30 AWG 7 strand, color coded PTFE wire, 36 inches.                                                            |
| 1-1589065-0 | 1589065 | TCM044PC2DMC46 | Threaded coupling, circular, metal, 44 position, plug, 30AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 46 centimeters. |
| 1-1589065-1 | 1589065 | TCM044PC2DM036 | Threaded coupling, circular, metal, 44 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 36 inches.     |
| 1-1589065-2 | 1589065 | TCM044PC2DC020 | Threaded coupling, circular, metal, 44 position, plug, 30 AWG 7 strand, color coded PTFE wire, 20 inches.                                                            |
| 1-1589065-3 | 1589065 | TCM044PC0DM036 | Threaded coupling, circular, metal, 44 position, plug, 28 AWG solid, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 36 inches.        |
| 1-1589065-4 | 1589065 | TCM044PC0DM048 | Threaded coupling, circular, metal, 44 position, plug, 28 AWG solid, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 48 inches.        |
| 1-1589065-5 | 1589065 | TCM044PC0DM060 | Threaded coupling, circular, metal, 44 position, plug, 28 AWG solid, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 60 inches.        |
| 1-1589065-6 | 1589065 | TCM044PC2DM120 | Threaded coupling, circular, metal, 44 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 120 inches.    |
| 1-1589065-7 | 1589065 | TCM044PC2DC024 | Threaded coupling, circular, metal, 44 position, plug, 30 AWG 7 strand, color coded PTFE wire, 24 inches.                                                            |
| 1-1589065-8 | 1589065 | TCM044PC2DMM01 | Threaded coupling, circular, metal, 44 position, plug, 30AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 1 meter.        |
| 2-1589065-0 | 1589065 | TCM044PC2DMC20 | Threaded coupling, circular, metal, 44 position, plug, 30AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 20 centimeters. |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TCM044PC0DM036](#)