

TE P/N	TE CD	Nanonics P/N	Part Description
1589070-1	1589070	CX010PC2RG006N	Coax, 50 ohm, 1 position, plug, 30AWG RG-178 coaxial cable, 6 inches, 1.0 captive jackscrews.
1589070-2	1589070	CX010PC2RG018N	Coax, 50 ohm, 1 position, plug, 30AWG RG-178 coaxial cable, 18 inches, 1.0 captive jackscrews.
1589070-3	1589070	CX010PC2RG072N	Coax, 50 ohm, 1 position, plug, 30AWG RG-178 coaxial cable, 72 inches, 1.0 captive jackscrews.
1589070-4	1589070	CX020PC2RG018N	Coax, 50 ohm, 2 position, plug, 30AWG RG-178 coaxial cable, 18 inches, 1.0 captive jackscrews.
1589070-5	1589070	CX030PC2RG006N	Coax, 50 ohm, 3 position, plug, 30 AWG RG-178 coaxial cable, 6 inches, 1.0 captive jackscrews.
1589070-6	1589070	CX030PC2RG012	Coax, 50 ohm, 3 position, plug, 30 AWG RG-178 coaxial cable, 12 inches.
1589070-7	1589070	CX030PC2RG012N	Coax, 50 ohm, 3 position, plug, 30 AWG RG-178 coaxial cable, 12 inches, 1.0 captive jackscrews.
1589070-8	1589070	CX030PC2RG018N	Coax, 50 ohm, 3 position, plug, 30 AWG RG-178 coaxial cable, 18 inches, 1.0 captive jackscrews.
1589070-9	1589070	CX030PC2RG020Q	Coax, 50 ohm, 3 position, plug, 30 AWG RG-178 coaxial cable, 20 inches, 1.2 captive jackscrews.
1-1589070-0	1589070	CX040PC2RG012N	Coax, 50 ohm, 4 position, plug, 30 AWG RG-178 coaxial cable, 12 inches, 1.0 captive jackscrews.
1-1589070-1	1589070	CX040PC2RG030N	Coax, 50 ohm, 4 position, plug, 30 AWG RG-178 coaxial cable, 30 inches, 1.0 captive jackscrews.
1-1589070-2	1589070	CX090PC2RG036N	Coax, 50 ohm, 9 position, plug, 30AWG RG-178 coaxial cable, 36 inches, 1.0 captive jackscrews.
1-1589070-3	1589070	CX010PC3CWC70N	Coax, 50 ohm, 1 position, plug, 32 AWG FEP insulated coaxial cable, 70 centimeters, 1.0 captive jackscrews.
1-1589070-4	1589070	CX050PC2RG006N	Coax, 50 ohm, 5 position, plug, 30 AWG RG-178 coaxial cable, 6 inches, 1.0 captive jackscrews.
1-1589070-5	1589070	CX080PC2RG036N	Coax, 50 ohm, 8 position, plug, 30 AWG RG-178 coaxial cable, 36 inches, 1.0 captive jackscrews.
1-1589070-6	1589070	CX080PC2RG048N	Coax, 50 ohm, 8 position, plug, 30 AWG RG-178 coaxial cable, 48 inches, 1.0 captive jackscrews.
1-1589070-7	1589070	CX040PC2RG060N	Coax, 50 ohm, 4 position, plug, 30 AWG RG-178 coaxial cable, 60 inches, 1.0 captive jackscrews.
1-1589070-8	1589070	CX020PC2RG060N	Coax, 50 ohm, 2 position, plug, 30AWG RG-178 coaxial cable, 60 inches, 1.0 captive jackscrews.
1-1589070-9	1589070	CX080PC2RG060N	Coax, 50 ohm, 8 position, plug, 30 AWG RG-178 coaxial cable, 60 inches, 1.0 captive jackscrews.
2-1589070-0	1589070	CX060PC2RGC10Q	Coax, 50 ohm, 6 position, plug, 30 AWG RG-178 coaxial cable, 10 centimeters, 1.2 captive jackscrews.
2-1589070-1	1589070	CX010PC2RGC10Q	Coax, 50 ohm, 1 position, plug, 30AWG RG-178 coaxial cable, 10 centimeters, 1.2 captive jackscrews.
2-1589070-2	1589070	CX080PC2RG006N	Coax, 50 ohm, 8 position, plug, 30 AWG RG-178 coaxial cable, 6 inches, 1.0 captive jackscrews.
2-1589070-3	1589070	CX070PC2RGC10Q	Coax, 50 ohm, 7 position, plug, 30AWG RG-178 coaxial cable, 10 centimeters, 1.2 captive jackscrews.
2-1589070-4	1589070	CX030PC2RG048N	Coax, 50 ohm, 3 position, plug, 30 AWG RG-178 coaxial cable, 48 inches, 1.0 captive jackscrews.
2-1589070-5	1589070	CX020PC2RG048N	Coax, 50 ohm, 2 position, plug, 30AWG RG-178 coaxial cable, 48 inches, 1.0 captive jackscrews.
2-1589070-6	1589070	CX030PC2RG060N	Coax, 50 ohm, 3 position, plug, 30 AWG RG-178 coaxial cable, 60 inches, 1.0 captive jackscrews.
2-1589070-7	1589070	CX080PC2RGC10N	Coax, 50 ohm, 8 position, plug, 30 AWG RG-178 coaxial cable, 10 centimeters, 1.0 captive jackscrews.
2-1589070-8	1589070	CX010PC2RG048Q	Coax, 50 ohm, 1 position, plug, 30 AWG RG-178 coaxial cable, 48 inches, 1.2 captive jackscrews.
2-1589070-9	1589070	CX080PC2RG024N	Coax, 50 ohm, 8 position, plug, 30 AWG RG-178 coaxial cable, 24 inches, 1.0 captive jackscrews.
3-1589070-0	1589070	CX060PC2RG036N	Coax, 50 ohm, 6 position, plug, 30 AWG RG-178 coaxial cable, 36 inches, 1.0 captive jackscrews.
3-1589070-1	1589070	CX060PC2RG072N	Coax, 50 ohm, 6 position, plug, 30 AWG RG-178 coaxial cable, 72 inches, 1.0 captive jackscrews.
3-1589070-2	1589070	CX060PC2RG144N	Coax, 50 ohm, 6 position, plug, 30 AWG RG-178 coaxial cable, 144 inches, 1.0 captive jackscrews.
3-1589070-3	1589070	CX060PC2RG012Q	Coax, 50 ohm, 6 position, plug, 30 AWG RG-178 coaxial cable, 12 inches, 1.2 captive jackscrews.
3-1589070-4	1589070	CX080PC2RG012Q	Coax, 50 ohm, 8 position, plug, 30 AWG RG-178 coaxial cable, 12 inches, 1.2 captive jackscrews.
3-1589070-5	1589070	CX060PC2RG018N	Coax, 50 ohm, 6 position, plug, 30AWG RG-178 coaxial cable, 18 inches, 1.0 captive jackscrews.
3-1589070-6	1589070	CX080PC2RG018N	Coax, 50 ohm, 8 position, plug, 30AWG RG-178 coaxial cable, 18 inches, 1.0 captive jackscrews.
3-1589070-7	1589070	CX040PC2RG039Q	Coax, 50 ohm, 4 position, plug, 30 AWG RG-178 coaxial cable, 39 inches, 1.2 captive jackscrews.
3-1589070-8	1589070	CX060PC2RG012N	Coax, 50 ohm, 6 position, plug, 30 AWG RG-178 coaxial cable, 12 inches, 1.0 captive jackscrews.
3-1589070-9	1589070	CX080PC2RG012N	Coax, 50 ohm, 8 position, plug, 30 AWG RG-178 coaxial cable, 12 inches, 1.0 captive jackscrews.
4-1589070-0	1589070	CX060PC2RG030Q	Coax, 50 ohm, 6 position, plug, 30 AWG RG-178 coaxial cable, 30 inches, 1.2 captive jackscrews.
4-1589070-1	1589070	CX040PC2RG036N	Coax, 50 ohm, 4 position, plug, 30 AWG RG-178 coaxial cable, 36 inches, 1.0 captive jackscrews.
4-1589070-2	1589070	CX080PC2RGC40N	Coax, 50 ohm, 8 position, plug, 30 AWG RG-178 coaxial cable, 40 centimeters, 1.0 captive jackscrews.
4-1589070-3	1589070	CX050PC2RGM02N	Coax, 50 ohm, 5 position, plug, 30 AWG RG-178 coaxial cable, 2 meters, 1.0 captive jackscrews.
4-1589070-4	1589070	CX020PC2RG036N	Coax, 50 ohm, 2 position, plug, 30 AWG RG-178 coaxial cable, 36 inches, 1.0 captive jackscrews.
4-1589070-5	1589070	CX040PC2RG020M	Coax, 50 ohm, 4 position, plug, 30 AWG RG-178 coaxial cable, 20 inches, 1.0 non-captive jackscrews.
4-1589070-6	1589070	CX080PC2RGC40Q	Coax, 50 ohm, 8 position, plug, 30 AWG RG-178 coaxial cable, 40 centimeters, 1.2 captive jackscrews.
4-1589070-7	1589070	CX030PC2RGM03N	Coax, 50 ohm, 3 position, plug, 30 AWG RG-178 coaxial cable, 3 meters, 1.0 captive jackscrews.
4-1589070-8	1589070	CX050PC2RG018N	Coax, 50 ohm, 5 position, plug, 30 AWG RG-178 coaxial cable, 18 inches, 1.0 captive jackscrews.
4-1589070-9	1589070	CX040PC2RG018N	Coax, 50 ohm, 4 position, plug, 30 AWG RG-178 coaxial cable, 18 inches, 1.0 captive jackscrews.
5-1589070-0	1589070	CX050PC2RG018Q	Coax, 50 ohm, 5 position, plug, 30 AWG RG-178 coaxial cable, 18 inches, 1.2 captive jackscrews.
5-1589070-1	1589070	CX090PC2RG060Q	Coax, 50 ohm, 9 position, plug, 30 AWG RG-178 coaxial cable, 60 inches, 1.2 captive jackscrews.
5-1589070-2	1589070	CX020PC2RG012N	Coax, 50 ohm, 2 position, plug, 30AWG RG-178 coaxial cable, 12 inches, 1.0 captive jackscrews.
5-1589070-3	1589070	CX020PC2RG072Q	Coax, 50 ohm, 2 position, plug, 30 AWG RG-178 coaxial cable, 72 inches, 1.2 captive jackscrews.
5-1589070-4	1589070	CX050PC2RG072Q	Coax, 50 ohm, 5 position, plug, 30 AWG RG-178 coaxial cable, 72 inches, 1.2 captive jackscrews.
5-1589070-5	1589070	CX030PC3CW018N	Coax, 50 ohm, 3 position, plug, 32 AWG FEP insulated coaxial cable, 18 inches, 1.0 captive jackscrews.
5-1589070-6	1589070	CX030PC2RG036N	Coax, 50 ohm, 3 position, plug, 30 AWG RG-178 coaxial cable, 36 inches, 1.0 captive jackscrews.
5-1589070-7	1589070	CX050PC2RG036N	Coax, 50 ohm, 5 position, plug, 30 AWG RG-178 coaxial cable, 36 inches, 1.0 captive jackscrews.
5-1589070-8	1589070	CX070PC2RG036N	Coax, 50 ohm, 7 position, plug, 30AWG RG-178 coaxial cable, 36 inches, 1.0 captive jackscrews.
5-1589070-9	1589070	CX030PC2RG048Q	Coax, 50 ohm, 3 position, plug, 30 AWG RG-178 coaxial cable, 48 inches, 1.2 captive jackscrews.
6-1589070-0	1589070	CX050PC2RG030N	Coax, 50 ohm, 5 position, plug, 30 AWG RG-178 coaxial cable, 30 inches, 1.0 captive jackscrews.
6-1589070-1	1589070	CX030PC2RG024Q	Coax, 50 ohm, 3 position, plug, 30 AWG RG-178 coaxial cable, 24 inches, 1.2 captive jackscrews.
6-1589070-2	1589070	CX090PC2RG018Q	Coax, 50 ohm, 9 position, plug, 30 AWG RG-178 coaxial cable, 18 inches, 1.2 captive jackscrews.
6-1589070-3	1589070	CX020PC2RG030N	Coax, 50 ohm, 2 position, plug, 30 AWG RG-178 coaxial cable, 30 inches, 1.0 captive jackscrews.
6-1589070-4	1589070	CX090PC2RG024N	Coax, 50 ohm, 9 position, plug, 30AWG RG-178 coaxial cable, 24 inches, 1.0 captive jackscrews.
6-1589070-5	1589070	CX070PC2RGM02Q	Coax, 50 ohm, 7 position, plug, 30AWG RG-178 coaxial cable, 2 meters, 1.2 captive jackscrews.
6-1589070-6	1589070	CX090PC2RG024Q	Coax, 50 ohm, 9 position, plug, 30 AWG RG-178 coaxial cable, 24 inches, 1.2 captive jackscrews.
6-1589070-7	1589070	CX090PC2RG060N	Coax, 50 ohm, 9 position, plug, 30AWG RG-178 coaxial cable, 60 inches, 1.0 captive jackscrews.
6-1589070-8	1589070	CX090PC2RG036Q	Coax, 50 ohm, 9 position, plug, 30AWG RG-178 coaxial cable, 36 inches, 1.2 captive jackscrews. Coax, 50 ohm, 9 position, plug, 30AWG RG-178 coaxial cable, 36 inches, 1.2 captive jackscrews



Nanonics Standard Catalog Part Number Cross-Reference

Revision 1

6-1589070-9	1589070	CX090PC2RG048Q	Coax, 50 ohm, 9 position, plug, 30AWG RG-178 coaxial cable, 48 inches, 1.2 captive jackscrews. Coax, 50 ohm, 9 position, plug, 30AWG RG-178 coaxial cable, 48 inches, 1.2 captive jackscrews.
7-1589070-0	1589070	CX040PC2RG048Q	Coax, 50 ohm, 4 position, plug, 30 AWG RG-178 coaxial cable, 48 inches, 1.2 captive jackscrews. Coax, 50 ohm, 4 position, plug, 30 AWG RG-178 coaxial cable, 48 inches, 1.2 captive jackscrews.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[CX080PC2RGC10N](#)