


ECN #	APPRVD.	DATE	REV.
/			

Ground Terminal
8-32 Screw
(2 Places)

Phoenix VDFK6
(6 Places)



SPECIFICATION

25Amp /40°C 50-60Hz

440VAC Phase to Phase


250VAC Phase to Neutral/Gnd

ATTENUATION

Comm.Mode - 70dB μ V at 100kHz

Dif.Mode - 80dB μ V at 100kHz

EQUIVALENT SCHEMATIC MEASURED AT 1kHz




Max. Leakage current at 10% unsymmetrical
mains, each Line to Ground:

2,5mA at 120V 60Hz

4,3mA at 250V 50Hz

THIRD ANGLE PROJECTION



This document is proprietary to CORCOM INC. and is not
to be reproduced nor used for manufacturing purposes
except on CORCOM'S order or prior written consent.



RFI FILTER

CAD FILE: cde\prt\cd\F7751

SCALE: .34	DATE: 2-12-96	DRG. NO.	REV.
DRW. BY: MS	DRG: MS	25FCD10	00

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[25FCD10](#)