

REV. 0

DCO 141447

COIL: @ 25°C

RESISTANCE 720 OHMS ±10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 13.5 VDC

MUST RELEASE 8.1 VDC MAX., 1.5 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 4 MS MAX.

RELEASE 4 MS MAX.

CONTACT BOUNCE 2 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
2 AMPS 28 VDC RESISTIVE
100,000 OPERATIONS

DR. B.D. 10/26/99 CKGAH 10/26/99

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. OPL

CUST. NO. M39016/14-002L REV.

'3SBH' RELAY

3SBH1142A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[M39016/14-002L](#)