





LOC	DIST	REVISIONS					
AD	39	P	LTR	DESCRIPTION	DATE	DWN	APVD
			P3	REVISED PER ECO-11-004587	11MAR11	RK	HMR



- ① PART NO. OBSOLETE
- ② .000015 GOLD ON CONTACT AREA G
.000100-.000200 BRIGHT TIN-LEAD
ON SOLDER LEADS, ALL OVER
.000050 NICKEL
- ③ RECESSED DATE CODE AND CSA LOGO
- ④ POINT OF MEASUREMENT FOR
PLATING THICKNESS
- ⑤ .000015 GOLD ON CONTACT AREA G
.000100-.000200 MATTE TIN ON
SOLDER LEADS, ALL OVER .000050
NICKEL
- ⑥ ROHS 2002/95/EC COMPLIANT
- ⑦ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



SECTION M-M



G			.800	.400	4	10	 	7-102589-2		
			10.300	9.900	99	200		7-102589-1		
			7.300	6.900	69	140		7-102589-0		
			6.800	6.400	64	130	 	6-102589-9		
			4.600	4.200	42	86		6-102589-8		
			3.900	3.500	35	72	 	6-102589-7		
			5.800	.700	7	16		6-102589-6		
			5.800	5.400	54	110	 	6-102589-5		
			4.800	4.400	44	90	 	6-102589-4		
			2.300	1.900	19	40		6-102589-3		
			1.300	.900	9	20		6-102589-2		
			6.300	5.900	59	120	 	6-102589-1		
			3.800	3.400	34	70		6-102589-0		
			5.100	4.700	47	96	 	5-102589-9		
			.900	.500	5	12		5-102589-8		
			3.300	2.900	29	60		5-102589-7		
			1.500	1.100	11	24		5-102589-6		
			2.800	2.400	24	50		5-102589-5		
			1.800	1.400	14	30		5-102589-4		
			5.300	4.900	49	100	 	5-102589-3		
			2.100	1.700	17	36		5-102589-2		
			4.300	3.900	39	80	 	5-102589-1		
		F			.800	.400	4	10		2-102589-2
					10.300	9.900	99	200		2-102589-1
	7.300			6.900	69	140		2-102589-0		
	6.800			6.400	64	130		1-102589-9		
	4.600			4.200	42	86		1-102589-8		
	3.900			3.500	35	72		1-102589-7		
	1.100			.700	7	16		1-102589-6		
	5.800			5.400	54	110		1-102589-5		
	4.800			4.400	44	90		1-102589-4		
	2.300			1.900	19	40		1-102589-3		
	1.300			.900	9	20		1-102589-2		
	6.300			5.900	59	120		1-102589-1		
	3.800			3.400	34	70		1-102589-0		
	5.100			4.700	47	96		102589-9		
	.900			.500	5	12		102589-8		
	3.300			2.900	29	60		102589-7		
	1.500			1.100	11	24		102589-6		
	2.800			2.400	24	50		102589-5		
	1.800			1.400	14	30		102589-4		
	5.300			4.900	49	100		102589-3		
	2.100			1.700	17	36		102589-2		
	4.300			3.900	39	80		102589-1		
REMARKS	FINISH			"C"	"B"	"A"	NO OF POSN	PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J KNAUB 12-2-93		 TE Connectivity	
		CHK H PALEY 12-20-93			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± -		ASSY, HEADER, MOD II, .025 SQ POSTS .100 X.100CL -	
		1 PLC ± -			
		2 PLC ± -			
		3 PLC ± .005			
		4 PLC ± -			
ANGLES		± -		SIZE	
MATERIAL		FINISH		CAGE CODE	
HSG: FLAME RETARDANT		POSTS: SEE TABLE		DRAWING NO	
POLYESTER				RESTRICTED TO	
POST: PHOS BRONZE				A2 00779 C-102589	
		WEIGHT		SCALE	
		CUSTOMER DRAWING		4:1	
				SHEET 1 of 1	
				REV P3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[102589-2](#)