



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AA4	REVISED PER ECR-18-005503	30MAY2018	BDA	SG

- 1 MATING CONN P/N: □-1123722-□
- 2 APPLICABLE P.C.B LAYOUT: SEE FIG. 1
- 3 APPLICABLE P.C.B THICKNESS: 1.60
- 4 SKETCHES SHOW NO PINS MISSING.

- 6 PIN: POST TIN OVER BRASS
- 7 HOUSING: PBT, 30% GLASS, UL94-V0.
- 8 ○ : WITH PIN,
X : WITHOUT PIN.

- 10 SUPERSEDED BY 1744489-2.
- 11 SUPERSEDED BY 1744489-4.
- 12 SUPERSEDED BY 1744489-5.
- 13 SUPERSEDED BY 1744489-6.
- 14 SUPERSEDED BY 1744489-7.
- 15 SUPERSEDED BY 1744489-8.
- 16 SUPERSEDED BY 1744489-9.
- 17 SUPERSEDED BY 1-1744489-0.
- 18 SUPERSEDED BY 1-1744489-1.

VALUES FOR UL 61800-5-1				
Flam	RTIe deg C	HWI	HAI	CTI
V0	130	PLC 2	PLC 4	PLC 2_UL746



2 FIG.1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N.YAMASAKI 13MAR'01	TE Connectivity		
DIMENSIONS: mm		CHK M.SHINDO 13MAR'01			
		APVD Y.KASHIWA 13MAR'01	NAME 3.96MM PITCH ECONOMY POWER(EP) CONN HEADER ASSY		
		PRODUCT SPEC 108-5609			
MATERIAL SEE TABLE		FINISH SEE TABLE	SIZE A2	CAGE CODE 00779	DRAWING NO C=1123723
		WEIGHT	RESTRICTED TO —		
		CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 2	REV AA4

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT - By - ALL RIGHTS RESERVED.	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

[illegible]

											39.60	41.00	43.50	NATURAL	11		8-1123723-1			
																	GREEN		6-1123723-1	
																	BLACK		5-1123723-1	
																	RED		4-1123723-1	
																	BLUE		3-1123723-1	
																	YELLOW		2-1123723-1	
																	NATURAL		1-1123723-1	
											35.64	37.04	39.54	NATURAL	10		7-1123723-0			
																	GREEN		6-1123723-0	
																	BLACK		5-1123723-0	
																	RED		4-1123723-0	
																	BLUE		3-1123723-0	
																	YELLOW		2-1123723-0	
																	NATURAL		1-1123723-0	
											31.68	33.08	35.58	NATURAL	16		7-1123723-9			
	X				X						39.60	41.00	43.50	NATURAL			7-1123723-1			
											31.68	33.08	35.58	GREEN		9		6-1123723-9		
																		BLACK		5-1123723-9
																		RED		4-1123723-9
																		BLUE		3-1123723-9
																		YELLOW		2-1123723-9
																	NATURAL		1-1123723-9	
1	2	3	4	5	6	7	8	9	10	11	"C"	"B"	REF	"A"	REF	COLOR	POS	ASS'Y P/N		
PIN POSITION 											DIMENSION				COLOR	POS	ASS'Y P/N			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N.YAMASAKI 13MAR'01 CHK M.SHINDO 13MAR'01 APVD Y.KASHIWA 13MAR'01		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 0.50 2 PLC ± 0.30 3 PLC ± 4 PLC ± ANGLES ±		NAME 3.96MM PITCH ECONOMY POWER(EP) CONN HEADER ASSY	
		PRODUCT SPEC 108-5609		RESTRICTED TO	
MATERIAL SEE TABLE		APPLICATION SPEC —		SIZE A2	
FINISH SEE TABLE		WEIGHT —		CAGE CODE 00779	
CUSTOMER DRAWING		DRAWING NO C-1123723		SCALE 5:1	
SHEET 2 OF 2		REV AA4		SCALE 5:1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-1565036-4](#)