






	35.56 [1.400]	14	35.69 [1.484]	15	6-146129-3
	33.02 [1.300]	13	33.15 [1.384]	14	6-146129-2
	30.48 [1.200]	12	30.61 [1.284]	13	6-146129-1
	27.94 [1.100]	11	28.07 [1.184]	12	6-146129-0
	25.40 [1.000]	10	27.53 [1.084]	11	5-146129-9
	22.86 [.900]	9	24.99 [.984]	10	5-146129-8
	20.32 [.800]	8	22.45 [.884]	9	5-146129-7
	17.78 [.700]	7	19.91 [.784]	8	5-146129-6
	15.24 [.600]	6	17.37 [.684]	7	5-146129-5
	12.70 [.500]	5	14.83 [.584]	6	5-146129-4
	10.16 [.400]	4	12.29 [.484]	5	5-146129-3
	7.62 [.300]	3	9.75 [.384]	4	5-146129-2
	5.08 [.200]	2	7.21 [.284]	3	5-146129-1
	35.56 [1.400]	14	35.69 [1.484]	15	1-146129-3
	33.02 [1.300]	13	33.15 [1.384]	14	1-146129-2
	30.48 [1.200]	12	30.61 [1.284]	13	1-146129-1
	27.94 [1.100]	11	28.07 [1.184]	12	1-146129-0
	25.40 [1.000]	10	27.53 [1.084]	11	146129-9
	22.86 [.900]	9	24.99 [.984]	10	146129-8
	20.32 [.800]	8	22.45 [.884]	9	146129-7
	17.78 [.700]	7	19.91 [.784]	8	146129-6
	15.24 [.600]	6	17.37 [.684]	7	146129-5
	12.70 [.500]	5	14.83 [.584]	6	146129-4
	10.16 [.400]	4	12.29 [.484]	5	146129-3
	7.62 [.300]	3	9.75 [.384]	4	146129-2
	5.08 [.200]	2	7.21 [.284]	3	146129-1
PLATING	C	B	A	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: 9-30-94 J KNAUB CHK: 9-30-94 G DUBNICZKI APVD: 9-30-94 G DUBNICZKI		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.1% [.005] 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH		NAME SURFACE MOUNT HEADER ASSEMBLY, MOD II, BREAKAWAY, VERTICAL, SINGLE ROW, .100 X.100 C/L .025 SQ.POST	
		PRODUCT SPEC — APPLICATION SPEC —		SIZE A1	
MATERIAL 		WEIGHT —		CAGE CODE 00779	
SEE TABLE		DRAWING NO 146129		RESTRICTED TO —	
CUSTOMER DRAWING		SCALE 10:1		SHEET 1 OF 1 REV L	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[146129-1](#)