

LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	DWN
			E	REVISED PER ECR-07-002180	31JAN07	JR
						APVD
						GJ




1. SPECIFICATIONS:
MAGNET WIRE #8 - #34 AWG,
.040"(1.02mm) - .006"(0.16mm) DIA COPPER.
OTHER SIZES MAY BE ACCOMMODATED.
CONSULT TYCO ELECTRONICS FOR APPROVAL.

2. POCKET RECOMMENDATION: 1601425

3. SUPPLIED LOOSE PIECE ONLY

4 PRELIMINARY - NOT FOR PRODUCTION

5 TERMINAL APPLICATION TO COMPLY WITH TYCO
ELECTRONICS SPECIFICATION 114-13166 FIGURE 9.



SUPERSEDED BY 4-1601081-3

SUPERSEDED BY 4-1601081-2

-		-	-
-		-	-
PRE-TIN PLATE OVER NICKEL UNDERPLATE		-	4-1601081-3
PRE-SILVER PLATE OVER NICKEL UNDERPLATE		031-151-025	4-1601081-2
PRE-TIN PLATE OVER NICKEL UNDERPLATE		-	1601081-3
PRE-SILVER PLATE OVER NICKEL UNDERPLATE		131-151-025	1601081-2
FINISH		REFERENCE PART NUMBER	TYCO PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		STANDARD RANGE WIRE MULTI- BARB 76 MM CONTACTOR SIAMEZE TERMINAL	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		-	
0 PLC ± -		SIZE	
1 PLC ± -		CAGE CODE	
2 PLC ± .01[0.25]		DRAWING NO	
3 PLC ± .005[0.13]		RESTRICTED TO	
4 PLC ± -		-	
ANGLES ± 2°		A2 00779 C=1601081	
FINISH		SCALE 4:1	
SEE TABLE		SHEET 1 of 1	
MATERIAL		REV E	
BRASS, H04		CUSTOMER DRAWING	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-1601081-2](#)