



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		C4	REVISED PER ECR-08-022956	15SEP08	HMR	GJ

- 1 SPECIFICATIONS  
MAGNET WIRE: #27-#36 AWG,  
0.36-0.13 [.014-.005] mm DIA. COPPER  
LEAD WIRE: 0.8-0.3mm2 [#18-#22] AWG, STRANDED, BONDED, OR  
SOLID WITH PVC INSULATION. MAX INSULATION OUTSIDE DIA  
2.9mm [.115] NO STRIPPING REQUIRED. OTHER INSULATION  
TYPES MAY BE ACCOMMODATED, CONSULT  
TYCO ELECTRONICS FOR APPROVAL.
- 2 POCKET RECOMMENDATION: 1601421.  
ALTERNATE POCKET : #1601462.
- 3 TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS  
SPECIFICATION 114-13166 FIGURE 3 OR 4.



UNPLATED		-	4-1601117-1
UNPLATED		150-010-000	2-1601117-1
UNPLATED		150-003-000	1601117-1
FINISH		REFERENCE PART NUMBER	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DWN J.WELLER 11JAN2002 CHK M.FEHER 17DEC03 APVD K.RANDOLPH 11JAN2002		NAME	
DIMENSIONS: INCHES		FINE RANGE WIRE TO STD. WIRE SIAMEZE TERMINAL	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.25 [.01] 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± 2°		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL BRASS, H08		A2 00779 C=1601117	
SEE TABLE		SCALE 11:1 SHEET 1 of 1 REV C4	
CUSTOMER DRAWING			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1601117-1](#)