


1. SPECIFICATIONS:  
MAGNET WIRE #27 - #36 AWG,  
0.38mm (.015") - 0.13 (.005") DIA. COPPER  
OTHER SIZES MAY BE ACCOMMODATED,  
CONSULT TYCO ELECTRONICS FOR APROVAL.

2. POCKET RECOMMENDATION: #1601424

3

TERMINAL APPLICATION TO COMPLY WITH  
TYCO ELECTRONICS SPECIFICATION 114-13166  
FIGURE 5.



	SELECTIVE TIN PLATE OVER NICKEL	---	4-1601120-4
OBSOLETE	SELECTIVE POST TIN LEAD PLATE OVER NICKEL	050-011-119	4-1601120-2
	SELECTIVE TIN PLATE OVER NICKEL	---	2-1601120-4
OBSOLETE	SELECTIVE POST TIN LEAD PLATE OVER NICKEL	150-012-119	2-1601120-2
	UNPLATED	150-012-000	2-1601120-1
	SELECTIVE TIN PLATE OVER NICKEL	---	1601120-4
SUPERSEDED	SELECTIVE POST TIN LEAD PLATE OVER NICKEL	150-011-019	1601120-3
OBSOLETE	SELECTIVE POST TIN LEAD PLATE OVER NICKEL	150-011-119	1601120-2
	UNPLATED	150-011-000	1601120-1
	FINISH	REFERENCE P/N	TYCO PART NUMBER

1601120-( )

TERMINALS TO UNWIND FROM REELS AS SHOWN:

2-1601120-( )

BEAM OFFSETS TO FACE REEL CORE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	J.WELLER	11JAN2002
CHK	M.FEHER	11JAN2002
APVD	K.RANDOLPH	11JAN2002

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
INCHES	0 PLC ± -
	1 PLC ± -
	2 PLC ± .01[0.25]
	3 PLC ± .005[0.13]
	4 PLC ± -
	ANGLES ± 2°

MATERIAL	FINISH
BRASS, SPRING HARD	SEE TABLE

PRODUCT SPEC	108-2244
APPLICATION SPEC	3
WEIGHT	0.000000
CUSTOMER DRAWING	

NAME	FINE RANGE WIRE TO .040 X .020 P.C.B. SIAMEZE TERMINAL		
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C=1601120	-
SCALE	SHEET	REV	
1:3	1 of 1	E2	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1601120-1](#)