





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		C	REVISED PER ECR-08-021071	28AUG08	HMR	GJ

- 1 SPECIFICATIONS:
- MAGNET WIRE: 15-23 AWG, 1.47[.058] - 0.56[.022]
DIA COPPER.
- BLADE CONTACT: ACCEPTS 0.8[.032] THICK BLADE.
- 2 POCKET RECOMMENDATION: #1601437
- 3 TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS SPECIFICATION 114-13210.
- 4 CONSULT TYCO ELECTRONICS FOR PRODUCT AND APPLICATION SPECIFICS PRIOR TO FIRST USE.



LOOSE PIECE
CONFIGURATION
4-1601137-()



PRE-TIN PLATE OVER COPPER UNDERPLATE		151-003-014	1601137-2
FINISH		REFERENCE P/N	TE P/N
DWN J.WELLER 11JAN2002 CHK M.FEHER 11JAN2002 APVD K.RANDOLPH 11JAN2002 PRODUCT SPEC		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
APPLICATION SPEC		MEDIUM RANGE WIRE TO BLADE RECEPTACLE SIAMEZE TERMINAL	
WEIGHT -		SIZE A2	RESTRICTED TO -
CUSTOMER DRAWING		CAGE CODE 00779	REV C
		DRAWING NO C=1601137	
		SCALE 6:1	SHEET 1 of 1

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± 0.25[.010]
	2 PLC ± 0.13[.005]
	3 PLC ± -
	4 PLC ± -
ANGLES ± 2°	
MATERIAL BRASS, SPRING HARD	FINISH SEE TABLE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1601137-2](#)