




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		F1	REVISED PER ECR-07-029275	10DEC07	HMR	GJ

- 1 SPECIFICATIONS:
MAGNET WIRE #12 - #23 AWG,
2.06mm (.081")-0.56mm (.022") DIA COPPER.
OTHER SIZES MAY BE ACCOMMODATED,
CONSULT TYCO ELECTRONICS FOR APPROVAL.
- 2 POCKET RECOMMENDATION: #1601438
- 3 TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS
SPECIFICATION 114-13210 FIGURE 4.
- 4 PRELIMINARY - NOT FOR PRODUCTION.



-	-	-
-	-	-
-	-	-
UNPLATED	1/2 HARD COPPER ALLOY	2-1601139-3
PRE-TIN PLATE	SPRING HARD BRASS	2-1601139-2
UNPLATED	SPRING HARD BRASS	2-1601139-1
PRE-TIN PLATE	SPRING HARD BRASS	1601139-2
UNPLATED	SPRING HARD BRASS	1601139-1
FINISH	MATERIAL	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS: INCHES	DWN J.WELLER 22FEB2002	Tyco Electronics Corporation Harrisburg, PA 17105-3608
	CHK M.FEHER 25FEB02	
	APVD G. JACONO 25FEB02	NAME MEDIUM RANGE WIRE TO .250 X .032 TAB SIAMEZE TERMINAL
	PRODUCT SPEC 108-2239	
MATERIAL SEE TABLE	APPLICATION SPEC 3	SIZE A2
	FINISH SEE TABLE	CAGE CODE 00779
CUSTOMER DRAWING		DRAWING NO 1601139
SCALE 4:1		SHEET 1 of 1
		REV F1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1601139-2](#)