



MAGNET WIRE SIZE AWG [mm DIA]	SLOT DEPTH "X" ±.003 [±0.08]
#18-#21.5 [1.02-0.69]	.245 [6.22]
#22-#25.5 [0.65-0.43]	.233 [5.92]
#26-#29.5 [0.41-0.27]	.225 [5.72]
#30-#33.5 [0.25-0.17]	.220 [5.59]
#34-#36 [0.16-0.13]	.217 [5.51]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 05APR2002 MICHAEL S. FEHER CHK 05APR2002 GENE JACONO APVD 05APR2002 KURT A. RANDOLPH PRODUCT SPEC — APPLICATION SPEC 114-13166 WEIGHT —		tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME STANDARD TAB SIAMEZE POCKET SPECIFICATION	
		0 PLC ± - 1 PLC ± - 2 PLC ± .01 [0.25] 3 PLC ± .005 [0.13] 4 PLC ± .0010 [0.026] ANGLES ± 2°		SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C-1601425 —	
MATERIAL 		FINISH —		CUSTOMER DRAWING	
				SCALE 4:1 SHEET 1 of 1 REV B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1601020-2](#)