


| REVISIONS |     |                           |           |     |      |
|-----------|-----|---------------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|           | 3   | REVISED PER ECR-20-010947 | 04AUG2020 | GK  | KA   |



NOTE:

1 FOR PART NUMBERS SEE SHEET 3 OF 3.

2 MARK SHOULD BE CENTRALLY POSITIONED  $\pm 0.1\text{mm}$ .

3 WIDTH OF MARK DEPENDS ON CHARACTER PRINTED

|  |  |                                    |  |                    |                           |
|--|--|------------------------------------|--|--------------------|---------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>RAGHAVENDRA K<br>25MAR2013  | TE Connectivity  |                    |                           |
|  |  | CHK<br>KEAN ALAN<br>25MAR2013      |  |                    |                           |
| DIMENSIONS:<br>mm                      |  | APVD<br>MARIO APPELLO<br>25MAR2013 | NAME<br>SNAP-ON MARKER STB/STD SIZE 12 WITH APPLICATOR |                    |                           |
|  |  | PRODUCT SPEC                       | —  |                    |                           |
|  |  | APPLICATION SPEC                   | —  |                    |                           |
| MATERIAL<br>—                          |  | WEIGHT<br>—                        | SIZE<br>A3   | CAGE CODE<br>C2290 | DRAWING NO<br>C-1768045-1 |
|  |  | CUSTOMER DRAWING                   |  | SCALE<br>NTS       | SHEET<br>1 OF 3           |
|  |  |                                    |  | REV<br>3           |                           |





REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|------|-----|------|
|   | —   | SEE SHEET 1 | —    | —   | —    |

4

OBSOLETE PART

|   |  |  |  |  |  |
|---|--|--|--|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.  |  | DWN 25MAR2013<br>RAGHAVENDRA K         |  | <div> TE Connectivity</div> |  |
|   |  | CHK 25MAR2013<br>KEAN ALAN             |  |  |  |
| DIMENSIONS:<br>mm   |  | TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | NAME   |  |
|  |  | 0 PLC ± —                              |  | PRODUCT SPEC   |  |
|   |  | 1 PLC ± —                              |  | APPLICATION SPEC   |  |
|   |  | 2 PLC ± —                              |  | —  |  |
| MATERIAL<br>—   |  | 3 PLC ± —                              |  | SIZE   |  |
|   |  | 4 PLC ± —                              |  | CAGE CODE  |  |
|   |  | ANGLES ± —                             |  | DRAWING NO   |  |
| FINISH<br>—   |  | WEIGHT<br>—                            |  | RESTRICTED TO  |  |
| CUSTOMER DRAWING  |  |  |  | SCALE NTS  |  |
|   |  |  |  | SHEET 3 OF 3   |  |
|   |  |  |  | REV 3  |  |

| DESCRIPTION            | PART NO.               |
|------------------------|------------------------|
| STB12-0-0              | 4-1768039-4            |
| STB12-1-1              | 4-1768039-5            |
| STB12-2-2              | 4-1768039-6            |
| STB12-3-3              | 4-1768039-7            |
| STB12-5-5              | 4-1768039-8            |
| STB12-6-6              | 4-1768039-9            |
| STB12-7-7              | 5-1768039-0            |
| STB12-8-8              | 5-1768039-1            |
| STB12-BLANK-0          | 5-1768039-2            |
| STB12-BLANK-1          | 5-1768039-3            |
| STB12-BLANK-2          | 5-1768039-4            |
| STB12-BLANK-3          | 5-1768039-5            |
| STB12-BLANK-5          | 5-1768039-6            |
| STB12-BLANK-6          | 5-1768039-7            |
| STB12-BLANK-7          | 5-1768039-8            |
| STB12-BLANK-8          | 5-1768039-9            |
| STD12W/1-12            | 7-1768403-0            |
| STD12W-0               | 027608-000             |
| STD12W-1               | 028690-000             |
| STD12W-2               | 127922-000             |
| STD12W-3               | 869998-000             |
| STD12W-4               | 422284-000             |
| STD12W-5               | 329976-000             |
| STD12W-6               | 654200-000             |
| STD12W-7               | 727782-000             |
| STD12W-8               | 157886-000             |
| STD12W-9               | 612832-000             |
| STD12W-A               | 392758-000             |
| STD12W-AC              | 8-1768044-0            |
| STD12W-B               | 190370-000             |
| STD12W-BLANK           | 8-1768044-2            |
| STD12W-C               | 379242-000             |
| STD12W-COLON           | 227492-000             |
| STD12W-D               | 466552-000             |
| <del>STD12W-D-LC</del> | <del>8-1768044-4</del> |
| STD12W-DOT             | 8-1768044-5            |
| STD12W-E               | 952178-000             |

| DESCRIPTION  | PART NO.    |
|--------------|-------------|
| STD12W-EARTH | 8-1768044-6 |
| STD12W-F     | 242654-000  |
| STD12W-G     | 371912-000  |
| STD12W-H     | 544882-000  |
| STD12W-I     | 743644-000  |
| STD12W-J     | 925236-000  |
| STD12W-K     | 402858-000  |
| STD12W-L     | 372210-000  |
| STD12W-M     | 797170-000  |
| STD12W-MINUS | 9-1768044-3 |
| STD12W-N     | 224378-000  |
| STD12W-P     | 200490-000  |
| STD12W-PLUS  | 9-1768044-6 |
| STD12W-Q     | 881472-000  |
| STD12W-R     | 610526-000  |
| STD12W-S     | 958362-000  |
| STD12W-SLASH | 102828-000  |
| STD12W-T     | 080248-000  |
| STD12W-U     | 606344-000  |
| STD12W-V     | 244058-000  |
| STD12W-W     | 922324-000  |
| STD12W-X     | 151660-000  |
| STD12W-Y     | 976192-000  |
| STD12W-Z     | 928688-000  |
| STD12Y-0     | 9-1768044-8 |
| STD12Y-1     | 9-1768044-9 |
| STD12Y-2     | 1768045-1   |
| STD12Y-3     | 1768045-2   |
| STD12Y-4     | 1768045-3   |
| STD12Y-5     | 1768045-4   |
| STD12Y-6     | 1768045-5   |
| STD12Y-7     | 1768045-6   |
| STD12Y-8     | 1768045-7   |
| STD12Y-9     | 1768045-8   |
| STD12Y-A     | 1768045-9   |
| STD12Y-AC    | 1-1768045-0 |
| STD12W/1-48  | 8-1768710-0 |

| DESCRIPTION            | PART NO.               |
|------------------------|------------------------|
| STD12Y-B               | 1-1768045-2            |
| STD12Y-BLANK           | 1-1768045-3            |
| STD12Y-C               | 1-1768045-5            |
| STD12Y-COLON           | 1-1768045-6            |
| STD12Y-D               | 1-1768045-7            |
| STD12Y-DOT             | 1-1768045-9            |
| STD12Y-E               | 2-1768045-0            |
| STD12Y-EARTH           | 2-1768045-1            |
| STD12Y-F               | 2-1768045-3            |
| STD12Y-G               | 2-1768045-5            |
| <del>STD12Y-G-LC</del> | <del>2-1768045-6</del> |
| STD12Y-H               | 2-1768045-7            |
| STD12Y-I               | 2-1768045-9            |
| STD12Y-J               | 3-1768045-0            |
| STD12Y-K               | 3-1768045-1            |
| STD12Y-L               | 3-1768045-3            |
| STD12Y-M               | 3-1768045-5            |
| STD12Y-MINUS           | 3-1768045-6            |
| STD12Y-N               | 3-1768045-8            |
| STD12Y-P               | 4-1768045-0            |
| STD12Y-PLUS            | 4-1768045-1            |
| STD12Y-Q               | 4-1768045-2            |
| STD12Y-R               | 4-1768045-3            |
| STD12Y-S               | 4-1768045-5            |
| STD12Y-SLASH           | 4-1768045-6            |
| STD12Y-T               | 4-1768045-7            |
| STD12Y-U               | 4-1768045-8            |
| STD12Y-V               | 4-1768045-9            |
| STD12Y-W               | 5-1768045-0            |
| STD12Y-X               | 5-1768045-1            |
| STD12Y-Y               | 5-1768045-2            |
| STD12Y-Z               | 5-1768045-3            |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[STD12W-6](#)