




P	LTR	DESCRIPTION	DATE	DWN	APVD
	3	REVISED PER ECR-20-010947	04AUG2020	GK	AK




1 FOR PART NUMBERS SEE SHEET 3 OF 3.


2 MARK SHOULD BE CENTRALLY POSITIONED  $\pm 0.1$  mm

3 WIDTH OF MARK DEPENDS ON CHARACTER PRINTED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA K 25MAR2013		 TE Connectivity	
		CHK KEAN ALAN 25MAR2013			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		APVD MARIO APPELLO 25MAR2013		SNAP-ON MARKER STB/STD SIZE 21 WITH APPLICATOR	
		PRODUCT SPEC —		—	
		APPLICATION SPEC —		—	
MATERIAL —		FINISH —		SIZE A3	CAGE CODE C2290
		WEIGHT —		DRAWING NO C-1768047-5	
CUSTOMER DRAWING				RESTRICTED TO —	
				SCALE NTS	SHEET 1 OF 3
				REV 3	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA K 25MAR2013	 TE Connectivity		
		CHK KEAN ALAN 25MAR2013			
		APVD MARIO APPELLO 25MAR2013	NAME SNAP-ON MARKER STB/STD SIZE 21 WITH APPLICATOR		
		PRODUCT SPEC			
		APPLICATION SPEC			
		WEIGHT	SIZE A3	CAGE CODE C2290	RESTRICTED TO
		CUSTOMER DRAWING	SCALE NTS	SHEET 2 OF 3	REV 3

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

DESCRIPTION	PART NO.
STB21—BLANK—0	5—1768040—0
STB21—BLANK—2	5—1768040—2
STB21—BLANK—6	5—1768040—5
STB21—BLANK—8	5—1768040—7
STD21—APPLICATOR	1768047—5
STD21W—0	1768047—6
STD21W—1	303184—000
STD21W—2	563918—000
STD21W—3	884468—000
STD21W—4	666714—000
STD21W—5	263556—000
STD21W—6	557678—000
STD21W—7	375434—000
STD21W—8	871050—000
STD21W—9	025278—000
STD21W—A	138262—000
STD21W—B	846224—000
STD21W—BLANK	1768047—9
STD21W—C	315560—000
STD21W—D	937516—000
STD21W—DOT	1—1768047—2
STD21W—E	398254—000
STD21W—EARTH	1—1768047—3
STD21W—F	150770—000
STD21W—G	415068—000
STD21W—H	872820—000
STD21W—I	091456—000
STD21W—J	210862—000

DESCRIPTION	PART NO.
STD21W—K	236972—000
STD21W—L	144498—000
STD21W—M	151926—000
STD21W—MINUS	2—1768047—0
STD21W—N	148398—000
STD21W—P	852494—000
STD21W—PLUS	2—1768047—3
STD21W—Q	085934—000
STD21W—R	962458—000
STD21W—S	251560—000
STD21W—SLASH	764286—000
STD21W—T	650510—000
STD21W—U	461542—000
STD21W—V	023470—000
STD21W—W	034464—000
STD21W—X	316680—000
STD21W—Y	882830—000
STD21W—Z	475522—000
STD21Y—0	2—1768047—5
STD21Y—1	2—1768047—6
STD21Y—2	2—1768047—7
STD21Y—3	2—1768047—8
STD21Y—4	2—1768047—9
STD21Y—5	3—1768047—0
STD21Y—6	3—1768047—1
STD21Y—7	3—1768047—2
STD21Y—8	3—1768047—3
STD21Y—9	3—1768047—4

DESCRIPTION	PART NO.
STD21Y—A	3—1768047—5
STD21Y—B	3—1768047—8
STD21Y—BLANK	3—1768047—9
STD21Y—C	4—1768047—1
STD21Y—D	4—1768047—3
STD21Y—DOT	4—1768047—5
STD21Y—E	4—1768047—6
STD21Y—EARTH	4—1768047—7
STD21Y—F	4—1768047—9
STD21Y—G	5—1768047—1
STD21Y—H	5—1768047—3
STD21Y—I	5—1768047—5
STD21Y—J	5—1768047—6
STD21Y—K	5—1768047—7
STD21Y—L	5—1768047—9
STD21Y—M	6—1768047—1
STD21Y—MINUS	6—1768047—2
STD21Y—N	6—1768047—4
STD21Y—P	6—1768047—6
STD21Y—PLUS	6—1768047—7
STD21Y—Q	6—1768047—8
STD21Y—R	6—1768047—9
STD21Y—S	7—1768047—1
STD21Y—SLASH	7—1768047—2
STD21Y—T	7—1768047—3
STD21Y—U	7—1768047—4
STD21Y—V	7—1768047—5
STD21Y—W	7—1768047—6
STD21Y—X	7—1768047—7

DESCRIPTION	PART NO.
STD21Y—Y	7—1768047—8
STD21Y—Z	7—1768047—9
STB21—2—2	4—1768040—4
STB21—BLANK—3	5—1768040—3
STD21W—COLON	094158—000
STD21Y—AC	3—1768047—6
STD21Y—COLON	4—1768047—2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[STD21W-9](#)