




5. CUTTING BURR MAX. 1mm ALLOWED.



1776310-4 AS SHOWN

135.0	157.9	12	TSB150012	1-1776310-2
121.5	144.4	11	TSB150011	1-1776310-1
108.0	130.9	10	TSB150010	1-1776310-0
94.5	117.9	9	TSB150009	1776310-9
81.0	103.9	8	TSB150008	1776310-8
67.5	90.4	7	TSB150007	1776310-7
54.0	76.9	6	TSB150006	1776310-6
40.5	63.4	5	TSB150005	1776310-5
27.0	49.9	4	TSB150004	1776310-4
13.5	36.4	3	TSB150003	1776310-3
—	22.9	2	TSB150002	1776310-2
—	9.4	1	TSB150001	1776310-1
DIM B	DIM A	POSN	T & B PART NUMBER	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL		 TE Connectivity Ltd.	
		CHK C RICHARD			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± — 1 PLC ± 0.3 2 PLC ± 0.25 3 PLC ± — 4 PLC ± — ANGLES ± 2°		13.5MM PITCH TUNNEL CONNECTION EUROPA TERMINAL BLOCK	
		PRODUCT SPEC —		—	
MATERIAL SEE NOTES		APPLICATION SPEC —		SIZE	RESTRICTED TO
FINISH SEE NOTES		WEIGHT —		CAGE CODE	DRAWING NO
				A300779	C-1776310
CUSTOMER DRAWING				SCALE NTS	SHEET 1 OF 1
				REV P	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TSB150005](#)