

4		3		2		1													
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST		REVISIONS											
© COPYRIGHT - By -		ALL RIGHTS RESERVED.		FT		0		P		LTR		DESCRIPTION		DATE		DWN		APVD	
										B		REVISED PER ECO-11-023039		18FEB12		KH		MS	
MECHANICAL: HOUSING: THERMOPLASTIC, UL94V-2, BLACK. TERMINALS: BRASS, BRIGHT TIN PLATE. SCREWS: 6-32, STEEL, PLATED .0002 MIN ZINC W/ CLEAR CHROMATE COATING. UNLESS OTHERWISE SPECIFIED. TIGHTENING TORQUE: 8 IN-LB. ELECTRICAL: MAXIMUM CURRENT: 20A. OPERATING VOLTAGE: 600V. WIRE RANGE: 12-22 AWG. ENVIRONMENTAL: OPERATING TEMP.: -60°C TO 105°C 1 ALL SCREWS BOTTOMED, TORQUE 2 TO 4 IN-LBS																			
THIS DRAWING IS A CONTROLLED DOCUMENT.										DWN S SCHLGEL 6/12/06		TE Connectivity							
DIMENSIONS: INCHES										CHK S YODER 6/12/06									
										APVD S YODER 6/12/06		NAME							
										PRODUCT SPEC									
MATERIAL -										APPLICATION SPEC		SIZE A3 CAGE CODE 00779 DRAWING NO C-1776858 RESTRICTED TO -							
										WEIGHT -									
CUSTOMER DRAWING										SCALE NTS		SHEET 1 OF 1		REV B					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1776858-7](#)