











X-2103124-7
KEY G - TOP VIEW



- IDENTIFICATION MARKING ON THIS SURFACE CONTAINS ASSEMBLY P/N AND DATE CODE (YYDD). TEXT ORIENTATION, SIZE, AND LOCATION CAN VARY AS LONG AS TEXT IS ON SURFACE SHOWN AND READABLE.
- SHIELD SEAM CAN BE POSITIONED AS SHOWN OR ROTATED 180° FROM POSITION SHOWN.
- DELETED
- THESE DIMENSIONS DEFINE FASTENER SIZE LIMITS FOR PROPER COMPONENT FUNCTIONALITY. END USER MUST ENSURE FASTENER AND/OR WASHER DIAMETER IS 8.6 MM MIN FOR PROPER RETENTION. THESE ARE NOT PRODUCT FEATURES - NO INSPECTION REQUIRED FOR THESE ITEMS.
- SURFACE FINISH APPLIES TO AREAS SHOWN IN MOUNTING INTERFACE SPECIFICATION
6. USE WITH 2.8MM BLADE TERMINAL P/N:
2-2141598-2 FOR 1.0 - 2.5MM² WIRE
2-2141600-2 FOR >2.5 - 4.0MM² WIRE
7. USE WITH MQS RECEPTACLE P/N:
963715-6, 963715-5, 928999-6 OR 928999-5,
DEPENDING ON WIRE SIZE AND MATING PLUG USED
8. NOTE DELETED
- NOTE DELETED

2103124-1 SHOWN IN ALL VIEWS UNLESS NOTED
REFER TO SHEET 2 FOR ADDITIONAL PART NUMBER VIEWS

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
B2		ECO-14-008515	06JUN2014	YS

SILVER	G	1-2103124-7
SILVER	F	1-2103124-6
SILVER	E	1-2103124-5
SILVER	D	1-2103124-4
SILVER	B	1-2103124-2
SILVER	A	1-2103124-1
TIN	G	2103124-7
TIN	F	2103124-6
TIN	E	2103124-5
TIN	D	2103124-4
TIN	B	2103124-2
TIN	A	2103124-1
SHIELD FINISH		INDEX
		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. DEWILTE 30SEP2010	TE Connectivity	
		CHK T. DEWILTE 30SEP2010		
DIMENSIONS:		APVD T. DEWILTE 15APR2011	NAME	
mm		PRODUCT SPEC	HVA280 2P HEADER ASSY W/HVIL PLASTIC 1 PIECE CHART DRAWING	
		APPLICATION SPEC		
		408-10441	SIZE	
MATERIAL		WEIGHT 22.7 g	CAGE CODE DRAWING NO	
		CUSTOMER DRAWING	A100779C=2103124	
		SCALE 2:1	SHEET 1 OF 2	
			REV B2	

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
-	-	SEE SHEET 1	-	-

	X-2103124-1 (KEY A)	X-2103124-2 (KEY B)	X-2103124-4 (KEY D)	X-2103124-5 (KEY E)	X-2103124-6 (KEY F)	X-2103124-7 (KEY G)
FRONT VIEW	 X PA66-GF33	 X PA66-GF33	 X PA66-GF33	 X PA66-GF33	 X PA66-GF33	 X PA66-GF33
SIDE VIEW						
REAR VIEW						
INTERFACE VIEW - MOUNTING SIDE	 KEY A MOUNTING INTERFACE	 KEY B MOUNTING INTERFACE	 KEY D MOUNTING INTERFACE	 KEY E MOUNTING INTERFACE	 KEY F MOUNTING INTERFACE	 KEY G MOUNTING INTERFACE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.50

1 PLC ±0.50

2 PLC ±0.15

3 PLC ±0.05

4 PLC ±

ANGLES ±3

FINISH

APPROVED

DATE

30SEP2010

30SEP2010

15APR2011

PRODUCT SPEC

APPLICATION SPEC

408-10441

WEIGHT 22.7 g

CUSTOMER DRAWING

NAME

HVA280 2P HEADER ASSY W/HVIL - PLASTIC 1 PIECE CHART DRAWING

SIZE

A1

CAGE CODE

00779

DRAWING NO

2103124

RESTRICTED TO

-

TE Connectivity

SCALE 2:1

SHEET 2 OF 2

REV B2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2103124-4](#)