




KIT CONTENTS

VALUE	PRODUCT NUMBER	TCPN	DESCRIPTION	QUANTITY
10R	CRGH0402F10R	2176433-1	CRGH0402 1% 10R 0.1W	100
11R	CRGH0402F11R	2176433-2	CRGH0402 1% 11R 0.1W	100
12R	CRGH0402F12R	2176433-3	CRGH0402 1% 12R 0.1W	100
13R	CRGH0402F13R	2176433-4	CRGH0402 1% 13R 0.1W	100
15R	CRGH0402F15R	2176433-5	CRGH0402 1% 15R 0.1W	100
16R	CRGH0402F16R	2176433-6	CRGH0402 1% 16R 0.1W	100
18R	CRGH0402F18R	2176433-7	CRGH0402 1% 18R 0.1W	100
20R	CRGH0402F20R	2176433-8	CRGH0402 1% 20R 0.1W	100
22R	CRGH0402F22R	2176433-9	CRGH0402 1% 22R 0.1W	100
24R	CRGH0402F24R	1-2176433-0	CRGH0402 1% 24R 0.1W	100
27R	CRGH0402F27R	1-2176433-1	CRGH0402 1% 27R 0.1W	100
30R	CRGH0402F30R	1-2176433-2	CRGH0402 1% 30R 0.1W	100
33R	CRGH0402F33R	1-2176433-3	CRGH0402 1% 33R 0.1W	100
36R	CRGH0402F36R	1-2176433-4	CRGH0402 1% 36R 0.1W	100
39R	CRGH0402F39R	1-2176433-5	CRGH0402 1% 39R 0.1W	100
43R	CRGH0402F43R	1-2176433-6	CRGH0402 1% 43R 0.1W	100
47R	CRGH0402F47R	1-2176433-7	CRGH0402 1% 47R 0.1W	100
51R	CRGH0402F51R	1-2176433-8	CRGH0402 1% 51R 0.1W	100
56R	CRGH0402F56R	1-2176433-9	CRGH0402 1% 56R 0.1W	100
62R	CRGH0402F62R	2-2176433-0	CRGH0402 1% 62R 0.1W	100
68R	CRGH0402F68R	2-2176433-1	CRGH0402 1% 68R 0.1W	100
75R	CRGH0402F75R	2-2176433-2	CRGH0402 1% 75R 0.1W	100
82R	CRGH0402F82R	2-2176433-3	CRGH0402 1% 82R 0.1W	100
91R	CRGH0402F91R	2-2176433-4	CRGH0402 1% 91R 0.1W	100
100R	CRGH0402F100R	2-2176433-5	CRGH0402 1% 100R 0.1W	100
110R	CRGH0402F110R	2-2176433-6	CRGH0402 1% 110R 0.1W	100
120R	CRGH0402F120R	2-2176433-7	CRGH0402 1% 120R 0.1W	100
130R	CRGH0402F130R	2-2176433-8	CRGH0402 1% 130R 0.1W	100

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	BA	INITIAL RELEASE	25SEP2019	SR	AP




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUPREETH R 25SEP2019	 TE Connectivity		
		CHK ALLAN P 25SEP2019			
DIMENSIONS: mm		PRODUCT SPEC	NAME CRGH 0402 1% 10R-1M0 LAB-KIT		
		APPLICATION SPEC			
MATERIAL		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C=2176439-1
		CUSTOMER DRAWING	SCALE 60:1	SHEET 1 OF 3	REV BA

KIT CONTENTS

VALUE	PRODUCT NUMBER	TCPN	DESCRIPTION	QUANTITY
150R	CRGH0402F150R	2-2176433-9	CRGH0402 1% 150R 0.1W	100
160R	CRGH0402F160R	3-2176433-0	CRGH0402 1% 160R 0.1W	100
180R	CRGH0402F180R	3-2176433-1	CRGH0402 1% 180R 0.1W	100
200R	CRGH0402F200R	3-2176433-2	CRGH0402 1% 200R 0.1W	100
220R	CRGH0402F220R	3-2176433-3	CRGH0402 1% 220R 0.1W	100
240R	CRGH0402F240R	3-2176433-4	CRGH0402 1% 240R 0.1W	100
270R	CRGH0402F270R	3-2176433-5	CRGH0402 1% 270R 0.1W	100
300R	CRGH0402F300R	3-2176433-6	CRGH0402 1% 300R 0.1W	100
330R	CRGH0402F330R	3-2176433-7	CRGH0402 1% 330R 0.1W	100
360R	CRGH0402F360R	3-2176433-8	CRGH0402 1% 360R 0.1W	100
390R	CRGH0402F390R	3-2176433-9	CRGH0402 1% 390R 0.1W	100
430R	CRGH0402F430R	4-2176433-0	CRGH0402 1% 430R 0.1W	100
470R	CRGH0402F470R	4-2176433-1	CRGH0402 1% 470R 0.1W	100
510R	CRGH0402F510R	4-2176433-2	CRGH0402 1% 510R 0.1W	100
560R	CRGH0402F560R	4-2176433-3	CRGH0402 1% 560R 0.1W	100
620R	CRGH0402F620R	4-2176433-4	CRGH0402 1% 620R 0.1W	100
680R	CRGH0402F680R	4-2176433-5	CRGH0402 1% 680R 0.1W	100
750R	CRGH0402F750R	4-2176433-6	CRGH0402 1% 750R 0.1W	100
820R	CRGH0402F820R	4-2176433-7	CRGH0402 1% 820R 0.1W	100
910R	CRGH0402F910R	4-2176433-8	CRGH0402 1% 910R 0.1W	100
1K0	CRGH0402F1K0	4-2176433-9	CRGH0402 1% 1K0 0.1W	100
1K1	CRGH0402F1K1	5-2176433-0	CRGH0402 1% 1K1 0.1W	100
1K2	CRGH0402F1K2	5-2176433-1	CRGH0402 1% 1K2 0.1W	100
1K3	CRGH0402F1K3	5-2176433-2	CRGH0402 1% 1K3 0.1W	100
1K5	CRGH0402F1K5	5-2176433-3	CRGH0402 1% 1K5 0.1W	100
1K6	CRGH0402F1K6	5-2176433-4	CRGH0402 1% 1K6 0.1W	100
1K8	CRGH0402F1K8	5-2176433-5	CRGH0402 1% 1K8 0.1W	100
2K0	CRGH0402F2K0	5-2176433-6	CRGH0402 1% 2K0 0.1W	100

VALUE	PRODUCT NUMBER	TCPN	DESCRIPTION	QUANTITY
2K2	CRGH0402F2K2	5-2176433-7	CRGH0402 1% 2K2 0.1W	100
2K4	CRGH0402F2K4	5-2176433-8	CRGH0402 1% 2K4 0.1W	100
2K7	CRGH0402F2K7	5-2176433-9	CRGH0402 1% 2K7 0.1W	100
3K0	CRGH0402F3K0	6-2176433-0	CRGH0402 1% 3K0 0.1W	100
3K3	CRGH0402F3K3	6-2176433-1	CRGH0402 1% 3K3 0.1W	100
3K6	CRGH0402F3K6	6-2176433-2	CRGH0402 1% 3K6 0.1W	100
3K9	CRGH0402F3K9	6-2176433-3	CRGH0402 1% 3K9 0.1W	100
4K3	CRGH0402F4K3	6-2176433-4	CRGH0402 1% 4K3 0.1W	100
4K7	CRGH0402F4K7	6-2176433-5	CRGH0402 1% 4K7 0.1W	100
5K1	CRGH0402F5K1	6-2176433-6	CRGH0402 1% 5K1 0.1W	100
5K6	CRGH0402F5K6	6-2176433-7	CRGH0402 1% 5K6 0.1W	100
6K2	CRGH0402F6K2	6-2176433-8	CRGH0402 1% 6K2 0.1W	100
6K8	CRGH0402F6K8	6-2176433-9	CRGH0402 1% 6K8 0.1W	100
7K5	CRGH0402F7K5	7-2176433-0	CRGH0402 1% 7K5 0.1W	100
8K2	CRGH0402F8K2	7-2176433-1	CRGH0402 1% 8K2 0.1W	100
9K1	CRGH0402F9K1	7-2176433-2	CRGH0402 1% 9K1 0.1W	100
10K	CRGH0402F10K	7-2176433-3	CRGH0402 1% 10K 0.1W	100
11K	CRGH0402F11K	7-2176433-4	CRGH0402 1% 11K 0.1W	100
12K	CRGH0402F12K	7-2176433-5	CRGH0402 1% 12K 0.1W	100
13K	CRGH0402F13K	7-2176433-6	CRGH0402 1% 13K 0.1W	100
15K	CRGH0402F15K	7-2176433-7	CRGH0402 1% 15K 0.1W	100
16K	CRGH0402F16K	7-2176433-8	CRGH0402 1% 16K 0.1W	100
18K	CRGH0402F18K	7-2176433-9	CRGH0402 1% 18K 0.1W	100
20K	CRGH0402F20K	8-2176433-0	CRGH0402 1% 20K 0.1W	100

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUPREETH R 25SEP2019	 TE Connectivity			
		CHK ALLAN P 25SEP2019				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CRGH 0402 1% 10R-1M0 LAB-KIT		
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC		
				APPLICATION SPEC		
MATERIAL -		FINISH -		WEIGHT -		
CUSTOMER DRAWING				SCALE 60:1	SHEET 2 OF 3	REV BA


KIT CONTENTS

VALUE	PRODUCT NUMBER	TCPN	DESCRIPTION	QUANTITY
22K	CRGH0402F22K	8-2176433-1	CRGH0402 1% 22K 0.1W	100
24K	CRGH0402F24K	8-2176433-2	CRGH0402 1% 24K 0.1W	100
27K	CRGH0402F27K	8-2176433-3	CRGH0402 1% 27K 0.1W	100
30K	CRGH0402F30K	8-2176433-4	CRGH0402 1% 30K 0.1W	100
33K	CRGH0402F33K	8-2176433-5	CRGH0402 1% 33K 0.1W	100
36K	CRGH0402F36K	8-2176433-6	CRGH0402 1% 36K 0.1W	100
39K	CRGH0402F39K	8-2176433-7	CRGH0402 1% 39K 0.1W	100
43K	CRGH0402F43K	8-2176433-8	CRGH0402 1% 43K 0.1W	100
47K	CRGH0402F47K	8-2176433-9	CRGH0402 1% 47K 0.1W	100
51K	CRGH0402F51K	9-2176433-0	CRGH0402 1% 51K 0.1W	100
56K	CRGH0402F56K	9-2176433-1	CRGH0402 1% 56K 0.1W	100
62K	CRGH0402F62K	9-2176433-2	CRGH0402 1% 62K 0.1W	100
68K	CRGH0402F68K	9-2176433-3	CRGH0402 1% 68K 0.1W	100
75K	CRGH0402F75K	9-2176433-4	CRGH0402 1% 75K 0.1W	100
82K	CRGH0402F82K	9-2176433-5	CRGH0402 1% 82K 0.1W	100
91K	CRGH0402F91K	9-2176433-6	CRGH0402 1% 91K 0.1W	100
100K	CRGH0402F100K	9-2176433-7	CRGH0402 1% 100K 0.1W	100
110K	CRGH0402F110K	9-2176433-8	CRGH0402 1% 110K 0.1W	100
120K	CRGH0402F120K	9-2176433-9	CRGH0402 1% 120K 0.1W	100
130K	CRGH0402F130K	2176434-1	CRGH0402 1% 130K 0.1W	100
150K	CRGH0402F150K	2176434-2	CRGH0402 1% 150K 0.1W	100
160K	CRGH0402F160K	2176434-3	CRGH0402 1% 160K 0.1W	100
180K	CRGH0402F180K	2176434-4	CRGH0402 1% 180K 0.1W	100
200K	CRGH0402F200K	2176434-5	CRGH0402 1% 200K 0.1W	100
220K	CRGH0402F220K	2176434-6	CRGH0402 1% 220K 0.1W	100
240K	CRGH0402F240K	2176434-7	CRGH0402 1% 240K 0.1W	100
270K	CRGH0402F270K	2176434-8	CRGH0402 1% 270K 0.1W	100
300K	CRGH0402F300K	2176434-9	CRGH0402 1% 300K 0.1W	100

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

VALUE	PRODUCT NUMBER	TCPN	DESCRIPTION	QUANTITY
330K	CRGH0402F330K	1-2176434-0	CRGH0402 1% 330K 0.1W	100
360K	CRGH0402F360K	1-2176434-1	CRGH0402 1% 360K 0.1W	100
390K	CRGH0402F390K	1-2176434-2	CRGH0402 1% 390K 0.1W	100
430K	CRGH0402F430K	1-2176434-3	CRGH0402 1% 430K 0.1W	100
470K	CRGH0402F470K	1-2176434-4	CRGH0402 1% 470K 0.1W	100
510K	CRGH0402F510K	1-2176434-5	CRGH0402 1% 510K 0.1W	100
560K	CRGH0402F560K	1-2176434-6	CRGH0402 1% 560K 0.1W	100
620K	CRGH0402F620K	1-2176434-7	CRGH0402 1% 620K 0.1W	100
680K	CRGH0402F680K	1-2176434-8	CRGH0402 1% 680K 0.1W	100
750K	CRGH0402F750K	1-2176434-9	CRGH0402 1% 750K 0.1W	100
820K	CRGH0402F820K	2-2176434-0	CRGH0402 1% 820K 0.1W	100
910K	CRGH0402F910K	2-2176434-1	CRGH0402 1% 910K 0.1W	100
1M0	CRGH0402F1M0	2-2176434-2	CRGH0402 1% 1M0 0.1W	100

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 25SEP2019 SUPREETH R		 TE Connectivity	
		CHK 25SEP2019 ALLAN P			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CRGH 0402 1% 10R-1M0 LAB-KIT	
		0 PLC ±-		PRODUCT SPEC	
		1 PLC ±-		-	
		2 PLC ±-		APPLICATION SPEC	
		3 PLC ±-		-	
		4 PLC ±-		-	
		ANGLES ±-		WEIGHT	
MATERIAL		FINISH		SCALE	
-		-		60:1	
-		-		SHEET 3 OF 3	
CUSTOMER DRAWING				REV BA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2176439-1](#)