







4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

-

-

SEE SHEET 1

-

-

-

152.00 MAX

142.00 MAX

20.00 MAX

20.50 MAX

14.50 MIN

5.00 MIN

6.30

SHORT LATCH TYPE

SOFT TRAY	BOARD LOCK	BLUE(2935U)	BLUE(2935U)	0.00038 MIN	2.10	9-2199154-6
SOFT TRAY	BOARD LOCK	NATURAL	BLUE(2935U)	0.00038 MIN	2.10	9-2199154-3
SOFT TRAY	BOARD LOCK	NATURAL	GREEN(375C)	0.00038 MIN	2.67	9-2199154-2
SOFT TRAY	BOARD LOCK	GREEN(375C)	BLACK	0.00076 MIN	2.10	8-2199154-9
SOFT TRAY	BOARD LOCK	NATURAL	BLUE(2935U)	0.00038 MIN	2.67	8-2199154-8
SOFT TRAY	BOARD LOCK	NATURAL	YELLOW(107C)	0.00076 MIN	3.18	8-2199154-7
SOFT TRAY	BOARD LOCK	NATURAL	YELLOW(107C)	0.00038 MIN	3.18	8-2199154-6
SOFT TRAY	BOARD LOCK	NATURAL	BLUE(2935U)	0.00076 MIN	3.18	8-2199154-4
SOFT TRAY	BOARD LOCK	GREEN(375C)	BLACK	0.00050 MIN	3.18	8-2199154-3
SOFT TRAY	BOARD LOCK	NATURAL	BLUE(2935U)	0.00038 MIN	3.18	8-2199154-2
SOFT TRAY	BOARD LOCK	GREEN(375C)	BLACK	0.00076 MIN	2.67	8-2199154-1
SOFT TRAY	BOARD LOCK	BLUE(2935U)	BLUE(2935U)	0.00038 MIN	2.67	7-2199154-9
SOFT TRAY	BOARD LOCK	NATURAL	YELLOW(107C)	0.00076 MIN	2.67	6-2199154-9
SOFT TRAY	BOARD LOCK	BLUE(2935U)	BLUE(2935U)	0.00038 MIN	3.18	6-2199154-6
SOFT TRAY	BOARD LOCK	BLACK	BLACK	0.00076 MIN	3.18	6-2199154-4
SOFT TRAY	BOARD LOCK	NATURAL	BLACK	0.00076 MIN	3.18	6-2199154-0
SOFT TRAY	BOARD LOCK	BLACK	BLACK	0.00050 MIN	3.18	5-2199154-2
SOFT TRAY	BOARD LOCK	NATURAL	BLACK	0.00050 MIN	3.18	5-2199154-1
SOFT TRAY	BOARD LOCK	NATURAL	NATURAL	0.00076 MIN	3.18	2-2199154-6
SOFT TRAY	BOARD LOCK	NATURAL	NATURAL	0.00038 MIN	3.18	2-2199154-5
SOFT TRAY	BOARD LOCK	BLACK	BLACK	0.00038 MIN	3.18	2-2199154-3
SOFT TRAY	BOARD LOCK	NATURAL	BLACK	0.00038 MIN	3.18	2-2199154-1
SOFT TRAY	BOARD LOCK	NATURAL	NATURAL	0.00076 MIN	2.10	1-2199154-6
SOFT TRAY	BOARD LOCK	NATURAL	BLACK	0.00038 MIN	2.10	1-2199154-5
SOFT TRAY	BOARD LOCK	BLACK	BLACK	0.00076 MIN	2.10	1-2199154-4
SOFT TRAY	BOARD LOCK	NATURAL	NATURAL	0.00038 MIN	2.10	1-2199154-3
SOFT TRAY	BOARD LOCK	NATURAL	BLACK	0.00076 MIN	2.10	1-2199154-2
SOFT TRAY	BOARD LOCK	BLACK	BLACK	0.00038 MIN	2.10	1-2199154-1
SOFT TRAY	BOARD LOCK	NATURAL	NATURAL	0.00076 MIN	2.67	2199154-6
SOFT TRAY	BOARD LOCK	NATURAL	NATURAL	0.00038 MIN	2.67	2199154-5
SOFT TRAY	BOARD LOCK	BLACK	BLACK	0.00076 MIN	2.67	2199154-4
SOFT TRAY	BOARD LOCK	BLACK	BLACK	0.00038 MIN	2.67	2199154-3
SOFT TRAY	BOARD LOCK	NATURAL	BLACK	0.00076 MIN	2.67	2199154-2
SOFT TRAY	BOARD LOCK	NATURAL	BLACK	0.00038 MIN	2.67	2199154-1
PACKING STYLE	HOUSING STYLE	EXTRACTOR COLOR	HOUSING COLOR	CONTACT GOLD INTERFACE	DIM A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±1

1 PLC ±0.25

2 PLC ±0.15

3 PLC ±0.10

4 PLC ANGLES ±

FINISH

MATERIAL

-

DWN 18MAR2013 RICHARD MA

CHK 18MAR2013 SIMON LI

APVD 18MAR2013 COREI WANG

PRODUCT SPEC 108-115067

APPLICATION SPEC 501-115076

WEIGHT -

CUSTOMER DRAWING

18MAR2013

18MAR2013

18MAR2013

NAME SOCKET ASSEMBLY DDR4 DIMM,T/H TYPE 288 POSITION

SIZE A2

CAGE CODE 00779

DRAWING NO C-2199154

RESTRICTED TO -

SCALE 1:1

SHEET 3 OF 8

REV C8


TE Connectivity

SOCKET ASSEMBLY
DDR4 DIMM,T/H TYPE
288 POSITION

1471-9 (3/11)

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD

A1471-9 (3/11)



D

D

C

C

B

B

A

A

D

C

B


A

D

C

B

A



1. MATERIALS :
TRAY: PVC, COLOR: TRANSPARENT
BOX: CORRUGATED FIBERBOARD
TRANSPARENT BAG: PE
2. DIMENSIONS:
TRAY: L=343;W=305;H=32.5
BOX: L=365;W=323;H=200
3. QUANTITY:
80 PCS/TRAY
320 PCS/BOX
4. WEIGHT:
NET WEIGHT: 1.9KG
GROSS WEIGHT: 3.4KG

SOFT TRAY PACKING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 18MAR2013 RICHARD MA	TE Connectivity			
		CHK 18MAR2013 SIMON LI				
DIMENSIONS:		APVD 18MAR2013 COREL WANG	NAME			
mm		PRODUCT SPEC	SOCKET ASSEMBLY			
		108-115067	DDR4 DIMM, T/H TYPE			
		APPLICATION SPEC	288 POSITION			
		501-115076	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT	A200779	C-2199154	-	-
MATERIAL		CUSTOMER DRAWING	SCALE 1:1	SHEET 7 OF 8	REV C8	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-						

D

C

B


A

D

C

B

A



1. MATERIALS :
TRAY: HIPS, COLOR: BLACK
BOX: CORRUGATED FIBERBOARD
TRANSPARENT BAG: PE
2. DIMENSIONS:
TRAY: L=326;W=136;H=28.2
BOX: L=323;W=285;H=335
3. QUANTITY:
24 PCS/TRAY
480 PCS/BOX
4. WEIGHT:
NET WEIGHT: 3.0KG
GROSS WEIGHT: 6.7KG

HARD TRAY PACKING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RICHARD MA 18MAR2013	TE Connectivity			
DIMENSIONS: mm		CHK SIMON LI 18MAR2013				
		APVD COREI WANG 18MAR2013	NAME SOCKET ASSEMBLY DDR4 DIMM,T/H TYPE 288 POSITION			
		PRODUCT SPEC 108-115067	SIZE A200779			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 501-115076	CAGE CODE C-2199154		DRAWING NO	
MATERIAL		WEIGHT -	RESTRICTED TO -		SCALE 1:1	
-		CUSTOMER DRAWING	SHEET 8		OF 8	
			REV C8			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2199154-7](#)