





















CODINGS						
						
CODE A	CODE B	CODE C	CODE D	CODE E	CODE F	CODE Z
						
CODE G	CODE H	CODE J	CODE K	CODE L	CODE M	CODE O




RECOMMENDED PCB LAYOUT



NOTES

- 1 DETAILS OF DESIGN ARE LEFT TO TE CONNECTIVITY
- 2 HSD INTERFACE ACC. TO TE SPEC. 114-18950
- 3 PACKAGING: TAPE AND REEL
- 4 MARKING OF 100% TEST PASSED
- 5 FITS WITH HSD CONNECTOR 90 DEG. TE PN X-2208145-X AND HSD CONTACT 90 DEG. TE PN 2236774-1...-3 OR HSD CONNECTOR 180 DEG TE PN X-1823898-X AND HSD CONTACT 180 DEG. TE PN 2236772-1
- 6 ALL DIMENSIONS IN BRACKETS () FOR INFORMATION ONLY



WEIGHT [g]: 2.7

AS SHOWN CODING Z

SCALE 2:1

1														SHIELDING BODY	Zn ALLOY	SOLDER SIDE: TIN PLATING 3μm MIN. INTERFACE SIDE(OUTER CONTACT): NICKEL PLATING 3μm MIN.	4
4														CONTACT PIN	CuSn4	SOLDER SIDE: TIN PLATING 3μm MIN. INTERFACE SIDE: GOLD PLATING 0.8μm MIN.	3
1														CAVITY BLOCK	PA4T-GF30	BLACK	2
												1	O	CODING COVER	PA6T/6 -GF25		1
												1	M			LIGHT GREEN / 6027	
												1	L			PASTEL ORANGE / 2003	
												1	K			YELLOW GREEN / 6048	
												1	J			CURRY / 1027	
												1	H			BEIGE / 1001	
												1	G			HEATHER VIOLET / 4003	
												1	Z			BLUISH GREY / 7031	
												1	F			WATER BULE / 5021	
												1	E			NUT BROWN / 8011	
												1	D			LEAF GREEN / 6002	
												1	C			CLARET VIOLET / 4004	
												1	B			SIGNAL BLUE / 5005	
												1	A			CREAM WHITE / 9001	
												1				JET BLACK / 9005	

QUANTITY															CODE	DESCRIPTION	MATERIAL	FINISH COLOR, SIMILAR RAL	ITEM NO.
2-1	2-2	2-3	2-4	2-5	2-6	2-9	3-1	3-2	3-3	3-4	3-5	3-6	3-9			ASSY NO. X-2291364-Y			
A	B	C	D	E	F	Z	G	H	J	K	L	M	O			ASSY CODE			
B	B	B	B	B	B	B	B	B	B	B	B	B	B			REVISION			

1														SHIELDING BODY	Zn ALLOY	SOLDER SIDE: TIN PLATING 3μm MIN. INTERFACE SIDE(OUTER CONTACT): TIN PLATING 3μm MIN.	4
4														CONTACT PIN	CuSn4	SOLDER SIDE: TIN PLATING 3μm MIN. INTERFACE SIDE: GOLD PLATING 0.8μm MIN.	3
1														CAVITY BLOCK	PA4T-GF30	BLACK	2
												1	O	CODING COVER	PA6T/6 -GF25	LIGHT GREEN / 6027	1
												1	M			PASTEL ORANGE / 2003	
											1		L			YELLOW GREEN / 6048	
											1		K			CURRY / 1027	
											1		J			BEIGE / 1001	
											1		H			HEATHER VIOLET / 4003	
											1		G			BLUISH GREY / 7031	
											1		Z			WATER BULE / 5021	
											1		F			NUT BROWN / 8011	
											1		E			LEAF GREEN / 6002	
											1		D			CLARET VIOLET / 4004	
											1		C			SIGNAL BLUE / 5005	
											1		B			CREAM WHITE / 9001	
1													A			JET BLACK / 9005	

QUANTITY															CODE	DESCRIPTION	MATERIAL	FINISH COLOR, SIMILAR RAL	ITEM NO.
0-1	0-2	0-3	0-4	0-5	0-6	0-9	1-1	1-2	1-3	1-4	1-5	1-6	1-9			ASSY NO. X-2291364-Y			
A	B	C	D	E	F	Z	G	H	J	K	L	M	O			ASSY CODE			
B	B	B	B	B	B	B	B	B	B	B	B	B	B			REVISION			

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIMENSIONS: mm
TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0.5
1 PLC ±0.5
3 PLC ±0.5
4 PLC ±0.5
ANGLES ±0.5
FINISH

OWN F.PAN 01APR2015
CHK F.PAN 01APR2015
APVD P.WU 01APR2015

PRODUCT SPEC 108-101388
APPLICATION SPEC
WEIGHT
Customer Drawing

NAME HSD HEADER 180DEG 4POS. ASSY.
SIZE A1
CAGE CODE
DRAWING NO. C=2291364
RESTRICTED TO

SCALE 5:1
SHEET 1 OF 1
REV C

TE Connectivity

Customer Drawing

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2291364-9](#)