



D

C

B

A


SEE SHEET 2 FOR
WIRING COLOR CODE



NOTES:

1. MATERIALS:
HOUSING: GLASS-FILLED THERMOPLASTIC, UL 94V-0 RATED
DIMMING CONTACTS (2 OR 4): COPPER ALLOY
LINE VOLTAGE CONTACTS (3): COPPER ALLOY
SPRING PLATE: STAINLESS STEEL
LOCKING RING: PBT
2. FINISH:
DIMMING CONTACTS (2 OR 4): NICKEL UNDERPLATE ENTIRE CONTACT
0.127 µm MIN THICK. GOLD PLATE CONTACT PAD AREA (MATING FACE
SIDE ONLY) 0.76 µm MIN THICK. MATTE TIN PLATE TAB ON BOTH SIDES
0.30 µm MIN THICK.
LINE VOLTAGE CONTACTS (3): TIN PLATE.
3. LINE VOLTAGE CONDUCTORS (3):
14 AWG, 600V, 150°C RATED, COPPER 41/30 STRANDED
PER UL STYLE AWM 3321.
4. MATING INTERFACE PER ANSI C136.41-2013.
5. OPTIONAL DIMMING CONTACTS (2) SUPPLIED.
6. DIMMING CONDUCTORS (2 OR 4):
18 AWG, 600V, 150°C RATED, 16/30 STRANDED,
PER UL STYLE AWM 3321.
7. LINE VOLTAGE CONDUCTORS (3):
14 AWG, 600V, 105°C RATED, COPPER 41/30 STRANDED.
PER UL STYLE AWM 1015.
8. DIMMING CONDUCTORS (2 OR 4):
18 AWG, 600V, 105°C RATED, COPPER 16/30 STRANDED.
PER UL STYLE AWM 1015.
9. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)
10. LOCKING RING (REF P/N: 2333095-1) AND
SPRING PLATE (REF P/N: 2333094-1) NOT ASSEMBLED,
SHIPPED BULK PACKED
11. MUST BE USED WITH GASKET (REF P/N: 2332473-1) SOLD SEPARATELY

304.8	291.3	7 AND 8	4 5	2-2332966-4
304.8	291.3	7 AND 8	2	2-2332966-3
304.8	291.3	3 AND 6	4 5	2-2332966-2
304.8	291.3	3 AND 6	2	2-2332966-1
A	B	WIRE STYLE	QUANTITY OF DIMMING CONTACTS	PART NO.
WIRE LENGTH				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 15MAR2018	TE TE Connectivity			
		CHK E. HOWARD 15MAR2018				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD -	NAME RECEPTACLE ASSEMBLY, LUMAWISE ENDURANCE N TOOL-LESS ROTATABLE			
	0 PLC ± 1 PLC ±0.2 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±1° FINISH	PRODUCT SPEC 108-133114 APPLICATION SPEC 114-133114 WEIGHT -				
MATERIAL -			SIZE A2	CAGE CODE 00779	DRAWING NO C-2332966	RESTRICTED TO -
			CUSTOMER DRAWING			SCALE 1:1 SHEET 1 OF 3 REV A3

D

C

B

A

LOC	DIST	REVISIONS					
-	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

D

D

C


C

B


B

A

A



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 15MAR2018	TE Connectivity			
		CHK E. HOWARD 15MAR2018				
DIMENSIONS:		APVD -	NAME			
mm		PRODUCT SPEC	RECEPTACLE ASSEMBLY, LUMAWISE ENDURANCE N TOOL-LESS ROTATABLE			
		108-133114				
		APPLICATION SPEC	SIZE			
		114-133114	CAGE CODE			
MATERIAL		WEIGHT	DRAWING NO			
		-	RESTRICTED TO			
		-	A200779C-2332966			
		-	CUSTOMER DRAWING			
		-	SCALE 1:1			
		-	SHEET 2 OF 3			
		-	REV A3			



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2332966-4](#)